



## Stand Fan 40 cm 45 W Chrome Silver

### General information

Adjustable chrome stand fan to enjoy a refreshing breeze. It features a powerful motor with three settings (low, moderate and high), easy-to-operate buttons, an oscillation knob on top to control the distribution, and an adjustable tilt head to target the air flow.

### Features

- Easy-to-operate buttons
- Adjustable angle for the perfect air flow
- High-quality chrome finish which fits in any interior
- Robust and stable design

### Specifications

Frequency:	50 Hz
Type:	Stand Fan
Colour:	Silver
Material:	Chrome
Input voltage:	230 V
Cable length:	1.8 m
Usage:	Cooling
Size:	40 cm
Power plug:	Euro / Type C (CEE 7/16)
Feature:	3-Speed
Feature:	Adjustable Angle
Feature:	Oscillation
Power:	45 W

### Package contents

1x stand fan  
manual



### Sales information

Order code: **KN-MSF16**  
 Product description: Stand Fan 40 cm 45 W Chrome Silver  
 Brand name: HQ



Quantity	LxWxH (mm)	Weight
1	470x165x595	7060 gr.
2	500x500x800	15000 gr.