


TRMS LEAKAGES CLAMP

METER 60Aac

DCM300LEAK



Terciario/
Residencial



Industria



- TRMS measurements
- 6000 count display
- AC current measurement up to 60A
- Leakage current measurement with 1 μ A resolution
- Switchable low-pass filter function
- Automatic range
- Readings hold
- MAX/MIN
- Torch
- Bluetooth connection with KPS Link application
- Safety category CATIII 600V

CE

UK
CA



Available on the
App Store

GET IT ON
Google Play



DCM300LEAK

TRMS LEAKAGES CLAMP METER 60Aac

General	
Display	6000 cuentas
Auto power off	✓
Backlight	✓
Hold	✓
Low-pass filter	50-60Hz/1kHz
Auto-ranging	✓
MIX/MAX	✓
Wireless connectivity	✓
Jaw Diameter	42m
Dimensions	100x230x24mm
Torch	✓
Weight	500g
Batteries	NEDA 15A/IEC LR6, 2*1,5V
Standars	EC 61010-1, IEC/EN61010-2-032
Safety category	CAT IV 600V, CAT III 1000V
Accesories included	Pouch

Specs	
TRMS	✓
AC Current	6mA-60A

Product Code Information	
SKU	KPSDCM300LEAKBTCBINT
EAN code	8435394784254
UPC code	810053673851
Pcs/export carton	20