

Digital Sound Level Meter

KPS-SN10



- Digital sound level meter
- Type II according to IEC 651
- 2000 counts
- Sampling rate: 2 times per second
- Frequencies captured: 30 Hz ~ 8kHz
- Indication of A and C weighted values
- FAST / SLOW selection
- Indication by numerical values and by bar graph
- Maximum values
- Hold readings on screen
- Automatic scale
- Backlit display
- Auto power off. Low battery indicator

KPS-SN10

Digital Sound Level Meter

General	
Product Size	193mm×60mm×29mm
Product Weight	222g
Power Supply	4×1.5V AAA Batteries
Certificate	CE/ETL/RoHS

Specs	
Display Counts	2000
Auto And Manual Ranging	✓
Auto Power Off	✓
Dynamic (50dB)	✓
Frequency	30Hz ~ 8kHz
Sample Rate	2 times/second
Fast/Slow	125ms/1 sec
A/C Weighting	✓
Display Backlight	✓
Low Battery Display	✓
Analog Bar Indication	✓
Over Range Indication	✓
MAX	✓
Data Hold	✓

KPS-SN10

Digital Sound Level Meter

UNITS	SCALE	RESOLUTION	ACCURACY
Sound Level	30 ~ 130 dB	0.1 dB	±1.5 dB

Product Code Information	
SKU	KPSSN10CBINT
EAN code	8435394710365
UPC code	810053670507
Pcs/export carton	40