

Product data sheet

Specifications

APC KVM 2G, Server Module, PS/2

KVM-PS2



Overview

Lead time Usually in Stock

Physical

Height 0.55 in (1.4 cm)

Width 4.92 in (12.5 cm)

Depth 4.92 in (12.5 cm)

Net Weight 0.29 lb(US) (0.13 kg)

Mounting preference No preference

Mounting Mode Not rack-mountable

Conformance

Product Certifications C-tick
CE
TAA compliance
VCCI Class A

Standards FCC Part 15 class A
ICES-003
UL 60950-1

Environmental

Ambient Air Temperature for Operation 32...122 °F (0...50 °C)

Operating altitude 0...10000 ft

Relative Humidity 5...95 %

Ambient Air Temperature for Storage 14...140 °F (-10...60 °C)

Storage altitude 0...50000 ft (0.00...15240.00 m)

Storage Relative Humidity 5...95 %

Ordering and shipping details

GTIN 731304286653

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1	1
Package 1 Height	1.65 in (4.2 cm)
Package 1 Width	5.08 in (12.9 cm)
Package 1 Length	4.92 in (12.5 cm)
Package 1 Weight	0.37 lb(US) (0.17 kg)
SCC14	10731304286650

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Recommended replacement(s)