



Mouse - in - a - Box® Wired

Comfort meets simplicity

K72356EU

Product Description

The Kensington Mouse-in-a-Box® USB provides reliable optical mouse performance for an attractive price and it's completely Plug & Play so it works with your computer, right out of the box.

Features

- Responsive and reliable optical 800dpi sensor
- Scroll wheel is ideal for speeding through documents
- A comfortable, contoured ambidextrous shape that is optimised for everyone
- Wired 180cm USB cable for battery free reliability
- PC and Mac® compatible

Specifications

- **CE Certificated** Unknown
- **Compatibility** Chrome OS 44 or above, macOS 10.10 or above, macOS 10.9, macOS X 10.11, Vista, Windows 10, Windows 7, Windows 8, XP
- **Sensor** Optical
- **Custom / Stock** Stock
- **Durable / Consumable** Durable
- **GS Certificated** Unknown
- **Connectivity** Wired
- **Controls** Scrollwheel

Product information

Depth	38mm
Width	55mm
Height	115mm
Gross weight	0.07kg

Retail Packaging Information

Depth	47mm
Width	90mm
Height	137mm
Gross weight	0.13kg
UPC#	5028252302814
Unit quantity	1

Master Case Information

Depth	240mm
Width	190mm
Height	160mm
Gross weight	1.51kg
UPC#	5028252302845
Unit quantity	10

Shipping Information

Country of origin	CN
Minimum Order Quantity	1
Warranty Period	60

General information

Colour	BLACK & GRAY
--------	--------------