

# Wireless ValuMouse

K72392EU



## Product information

Depth	38mm
Width	108mm
Height	60mm
Gross weight	0.17kg

## Retail Packaging Information

Depth	35mm
Width	132mm
Height	197mm
Gross weight	0.17kg
UPC#	5028252478656
Unit quantity	1

## Master Case Information

Depth	395mm
Width	155mm
Height	230mm
Gross weight	1.31kg
UPC#	5028252478663
Unit quantity	5

## Shipping Information

Country of origin	CN
Minimum Order Quantity	5

## General information

Colour	Black
--------	-------

## Product Description

The Wireless ValuMouse is ideal when you need a comfortable mouse that's also reduces cord clutter. The three-button/scroll wheel setup offers silent clicking when you need to get work done and don't want to disturb anyone. A high-definition optical sensor provides reliable and responsive control when you're navigating and the comfortable, contoured shaping feels great for either right-handed or left-handed users. It offers Plug & Play installation with a 2.4 GHz USB nano receiver and is built to last with a 5-year limited warranty.

## Features

- Silent clicking for quiet environments
- 2.4GHz wireless freedom with storable nano receiver
- Ambidextrous, contoured shape for either right-handed or left-handed users
- High-definition optical sensor (1000 DPI) for responsive control
- Three Button/Scroll Wheel setup
- Plug & Play installation with nano USB receiver
- Low battery indicator and on/off switch
- Built to last with a 5-year limited warranty
- Compatible with Windows® 8.1, 8, 7 and Mac OS X

## Specifications

- **Colour** Black
- **Sensor** Optical
- **Compatibility** Windows 8, Windows 7, Windows 8.1, Windows 10, Mac OS X 10.11
- **Wireless Type** 2.4Ghz
- **Controls** Scrollwheel
- **Features** Ambidextrous Design, Wireless USB Receiver Storage