



97

97 Crimping Pliers "PreciForce"



97 52 36



97 52 38



97 52 30



97 52 33











97 52 34



97 52 35



97 52 50



- ▶ for solder-free electrical connections
- ▶ repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- ▶ these tools have been set precisely (calibrated) in the factory
- ▶ high transmission of force thanks to lever action for fatigue-reduced working
- ▶ good handling thanks to favourable handle position, low weight, short design and ergonomically shaped handles
- ▶ all stressed parts are made of special steel, oil-hardened and tempered
- ▶ head burnished, two-colour dual component handles

KNIPEX special

The new Crimping Pliers provide a very good handling and amazingly high leverage despite the compact size. Particularly favourable for larger cross sections.



several boxes can be connected with each other

Article-No.	EAN-Code	Range of Application	Capacity		Length		g
			mm ²	AWG	mm	g	
97 52 30	051855	non-insulated butt connectors	1.5-10.0	15-7	220	490	
97 52 33	051862	non-insulated terminals and plug connectors	0.5-10.0	20-7	220	490	
97 52 34	051879	non-insulated 4.8 mm	0.1-2.5	27-13	220	490	
97 52 35	051886	open plug-type 6.3 mm connectors	0.5-6.0	20-10	220	490	
97 52 36	051893	insulated terminals and connectors	0.5-6.0	20-10	220	490	
97 52 38	051909	end sleeves (ferrules)	0.5-6.0	20-10	220	490	
97 52 50	051916	COAX-BNC-Connectors RG 58, 174, 188, 316			220	490	
97 49 94	030947	locator for 97 52 34					
97 49 95	031000	locator for 97 52 35					