

## Product information

# 12 49 21

### Spare blades block



- Stripping without re-adjustment from 0.03 to 10.0 mm<sup>2</sup>
- Recessed wire cutter
- Universal blade geometry – robust and more durable
- Fully automatic adjustment to fine-stranded conductors with standard insulation throughout the entire capacity range from 0.03 to 10.0 mm<sup>2</sup>
- No damage to the conductors
- The clamping jaws made of steel hold the cable in a way that prevents slipping without damaging the remaining insulation
- With recessed wire cutter for Cu and Al conductors, stranded up to 10 mm<sup>2</sup> and single wire up to 6 mm<sup>2</sup>
- Particularly smooth-running mechanics and very low weight
- Replaceable blades block and length stop
- Handle with soft-plastic zone for a steady grip
- Body: glass fibre reinforced plastic
- Blade: special tool steel, oil-hardened



### General

Article No.	12 49 21
EAN	4003773057581
Weight	8 g
Dimensions	51 x 17 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

AWG	32 — 8
-----	--------

*technical change and errors excepted*