

VGA Extension Cable VGA Male - VGA Female 2.00 m Anthracite

General information

Cable to connect a beamer to a PC.

Features

- 24 ct gold-plated contacts for an outstanding image quality
- Full copper conductor to ensure superior transmission properties
- Double shielding for enhanced reduction of electromagnetic interference
- Durable moulded connectors specifically designed for intensive usage

Specifications

Connector design - side B:	Straight
Diameter:	7.0 mm
AWG value:	28
Plating:	Gold
Max. resolution:	1920x1200
Length:	2.00 m
Cable design:	Round
Connector design - side A:	Straight
Outside material:	PVC
Packaging:	Blister
Conductor material:	Copper
Colour:	Anthracite
Connection B:	VGA Female
Cable type:	VGA
Connection A:	VGA Male

Package contents

1x VGA extension cable



Sales information

Order code:	KNC59100E20
Product description:	VGA Extension Cable VGA Male - VGA Female 2.00 m Anthracite
Packaging:	Blister
Brand name:	König



Quantity	LxWxH (mm)	Weight
1	120x50x240	240 gr.
10	140x250x540	2635 gr.
40	300x520x550	11570 gr.