

# High Speed HDMI Cable HDMI Connector - VGA Female 0.20 m White

## General information

Convert HDMI™ video signals into VGA signals.

## Features

- 24 ct gold-plated contacts for an outstanding image quality
- Durable moulded connectors specifically designed for intensive usage
- Flexible strain relief to avoid cable fractures

## Specifications

Connector design - side B:	Straight
Diameter:	6.0 mm
Plating:	Gold
AWG value:	30
Max. resolution:	1920x1080
Length:	0.20 m
Cable design:	Round
Connector design - side A:	Straight
Outside material:	PVC
Packaging:	Blister
Conductor material:	Copper
Colour:	White
Connection B:	VGA Female
Connection A:	HDMI Connector
Cable type:	High Speed HDMI with Ethernet

## Package contents

1x HDMI™ adapter cable



## Sales information

Order code: **KNM34900W02**  
 Product description: High Speed HDMI Cable HDMI Connector - VGA Female 0.20 m White  
 Packaging: Blister  
 Brand name: König



Quantity	LxWxH (mm)	Weight
1	115x35x125	54 gr.
10	135x125x380	656 gr.
120	425x405x515	8750 gr.