CRESCENT LUFKIN SHOCKFORCE™ AND SHOCKFORCE NITE EYE™ MEASURING TAPES

Introducing the toughest tapes to ever hit a jobsite. Shockforce brings new meaning to the term high performance with a full 4,3 m / 14 feet* of standout and the ability to survive a 30 m / 100-foot drop. Add in a diamond coated 360-degree end hook that delivers 50% more gripping power, a two-sided blade with vertical markings on the back, and class-lead-ing ergonomics and you have a tape that's destined to be the new standard for trade professionals.

But that's not all. There's also the Shockforce Nite Eye, with all the capabilities of the original Shockforce plus the Nite Eye high visibility green-on-matte black blade. Made for superior legibility in any light condition – from bright sun to dim interiors – Shockforce Nite Eye helps you measure even faster.



SHOCKFORCE NITE EYE™ TAPE MEASURES

- Matte black nylon-coated blade provides extended product life and improved legibility in varied light conditions
- Diamond-coated end hook grabs material from every direction and prevents slippage
- Narrow blade technology offers reduced weight for carrying
- Optimized drum and spring design provides a compact case that fits comfortably in the palm of your hand
- Drop tested from 30 m / 100 feet for real life, on the job durability
- Dual-sided blade printed with vertical quick read scale on underside for overhead and hard-to-reach measurements
- Full 4,3 m / 14 feet of standout
- Steel tether point offers increased safety capability when working at height
- Tether point can also be used for scribing and drawing arcs during layout

TYPE / CODE NO.	BLADE SIZE		WEIGHT a
TTPE / GODE NO.	WIDTH	LENGTH	WEIGHTY
L1116BCM	30 mm	5 m	422
L1125BCM	30 mm	8 m	549

SHOCKFORCE™ TAPE MEASURES

- Matte nylon-coated blade provides extended product life and glare reduction
- Diamond-coated end hook grabs material from every direction and prevents slippage
- Narrow blade technology offers reduced weight for carrying
- Optimized drum and spring design provides a compact case that fits comfortably in the palm of your hand
- Drop tested from 30 m / 100 feet for real life, on the job durability
- Dual-sided blade printed with vertical quick read scale on underside for overhead and hard-to-reach measurements
- Full 4,3 m / 14 feet of standout
- Steel tether point offers increased safety capability when working at height
- Tether point can also be used for scribing and drawing arcs during layout

TYPE / CODE NO.	BLADE SIZE		WEIGHT
TTPE/ GODE NO.	WIDTH	LENGTH	WEIGHT g
L1116CM	30 mm	5 m	422
L1125CM	30 mm	8 m	549
L1116CME2	30 mm, 1-3/16 in	5 m, 16 ft	422
L1125CME2	30 mm, 1-3/16 in	8 m, 26 ft	549

TRUSTED BY THE TRADES



	BLADE STYLE	PACKAGING	SHELF PACK QTY.
SFN Carded 4	SFN	Carded	4
SFN Carded 4	SFN	Carded	4



BLADE STYLE	PACKAGING	SHELF PACK QTY.
SF1	Carded	4
SF1	Carded	4
SF2	Carded	4
SF2	Carded	4