



## LC-2 00840-PP6

LIGHTING CONNECTOR 2-POL, 0.08-4.0mm<sup>2</sup>, WITH LEVER, 6PCS/PACK

Lighting connector for both solid and stranded cable.

No tool needed.

Stripping length: 11 mm

Contact resistance:  $\leq 0.015 \Omega$

Insulation resistance:  $\geq 1000 M\Omega$

Material

Contact: Copper

Plastic parts: PC (Polycarbonate)

Spring: Stainless steel



### Product Properties:

Transparent	No
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes

Suitable for multi-wire core	Yes
Colour	Multi-coloured
Packaging	Bag
Number of clamp positions	4 .
Nominal voltage	600 V
Nominal current	32 A
Operating temperature	-40-105 °C

### **Dimensions:**

Unit	pck
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.08-2.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.08-4 mm <sup>2</sup>
Nominal voltage	600 V
Nominal cross section	0.2-4 mm <sup>2</sup>
AWG-range	28-12 .
MOQ	10 .

### **Approvals:**

Approved according to UKCA	Ja
Approved according to CE	Yes

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (Latest, 14 June 2023)
SCIP	Not Applicable

### **Other information:**

Trademark	NECORE
ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Product Group	106026
Search Description	KOPPLINGSPLINT, 2-POL, 0.08-2.5MM2(4MM2 SOLID)
Alternative SKU	LC-200840-PP6

### **Logistic information:**

Barcode	733117641185
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Packaging	Bag
Stock code	LC-2 00840-PP6
Taric code	85369010

Unit

pck

---

MOQ

10 .