



LC-5 0225

E1441276

LIGHTING CONNECTOR, 5-POL 0.08-2.5mm²(4mm² Solid), AWG 28-12, WITH LEVER

Lighting connector for both solid and stranded cable.

No tool needed.

Stripping length: 11 mm

Contact resistance: $\leq 0.015 \Omega$

Insulation resistance: $\geq 1000 M\Omega$

Material

Contact: Copper

Plastic parts: PC (Polycarbonate)

Spring: Stainless steel



Product Properties:

Transparent	No
With operation lever	Yes
Suitable for solid core	Yes

Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Multi-coloured
Packaging	Bag
Number of clamp positions	10 .
Nominal voltage	600 V
Nominal current	32 A
Operating temperature	-40-105 °C

Dimensions:

Unit	pcs
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.08-2.5 mm ²
Conductor cross section solid (solid, stranded)	0.08-4 mm ²
Nominal voltage	600 V
Nominal cross section	0.2-4 mm ²
AWG-range	28-12 .
MOQ	25 .

Approvals:

Approved according to UKCA	Ja
Approved according to CE	Yes

Compliance:

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (Latest, 14 June 2023)
SCIP	Not Applicable

Other information:

Trademark	NEMIQ
ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Product Group	106026
Search Description	KOPPLINGSPLINT, 5-POL
Alternative SKU	LC-50225

Logistic information:

Barcode	733117641169
E-no	E1441276
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Packaging	Bag

Stock code	LC-5 0225
Taric code	85369010
Unit	pcs
MOQ	25 .