

PRODUCT DATA SHEET H8R





2 - PRODUCT DATA SHEET v181203



PRODUCT DESCRIPTION

With this headlamp you always have your hands free for your project, your hobby or just in case. Because the H8R adjusts perfectly to your head, thanks to its ergonomic design and is easy to handle. That way you always have the best view and even better: the red rear light makes sure you're being seen by everyone else. And one more highlight: you can simply charge it anywhere in the world via USB.

- Environment-friendly and comfortable modern battery technology for a short charging time via USB 3.0 with charge indicator
- More security and visibility integrated rear light
- Simple operation Smart Light Technology: 1 switch, 3 light functions
- From the homogeneous circle of close range lighting (focused) to a sharply bundled long-distance beam (defocused) – the patented³ Advanced Focus System with reflector lense enables efficient, tailored lighting
- Quick modification of the light cone with just one hand Rapid Focus



TECHNICAL DATA	
Head diameter [mm]	36
Weight incl. batteries [g]	158
Weight without batteries [g]	110
Focus function	Yes
Head material	Aluminum alloy
Tube material	Other plastics
Optic	Plastic lense (PMMA)
Headband material	Elastic fabric
Headband type	Side headband
Head movement type	Stepped movement
Head movement angle [°]	65
Headband specifications	Detachable.
Headband specifications	Detachable,
neaubanu specincations	Elastic,

POWER SUPPLY	
Power source type	Rechargeable battery
Battery quantity	1
Battery type	Li-ion
Battery description	18650 3.7V
Total battery voltage [V]	3.7
Total battery capacity [mAh]	3400
Total battery energy ² [Wh]	12.58
Rechargeable	Yes
UN number	UN 3481
Charging time ⁵ [min]	360
Energy modes	Energy Saving
Energy status indicator	Charge Indicator, Low Battery Warning

FURTHER SPECIFICATIO	NS
IP class	IP54
Drop test (drop height) [m]	2
Working temperature range [°C]	-20 to +40

LIGHT FUNCTIONS

Power, Mid Power, Low Power

LIGHT SOURCE	
Amount LEDs	1
LED type	Xtreme LED
Color	White
Color temperature [K]	6000 to 8000
Color rendering index (CRI)	65

LIGHT VALUES	·)			
ANSI – Energy Saving	Boost	Power	Mid Power	Low Power
Light output ¹ [lm]		600	250	10
Beam distance ¹ [m]		150	100	20
Run time ¹ [h]		10	15	120

SWITCH		
Front Switch		

FEATURES

Rear light , Transportation lock

TECHNOLOGIES

Advanced Focus System³, Smart Light Technology, Temperature Control System, Rapid Focus



3 - PRODUCT DATA SHEET V181203

H8R

PACKAGING AND LOGISTICS



Exemplary Packaging Illustration



Exemplary Packaging Illustration

PACKAGING INFORMATION

Type of packaging	Blister
Scope of delivery	1 set of rechargeable batteries, USB cable
Item No.	500852
Customs tariff number	85131000
Color	black
MSRP price (€)	79.90

SIN	IGL	E PACKAGE	

Dimensions W x H x D [cm]	17 x 23 x 9.3
Gross weight [g]	320
GTIN-13	4058205005593

INNER CARTON

Unit	6
Dimensions W x D x H [cm]	47.2 x 30.2 x 18.5
Gross weight [g]	2430
GTIN-13	4058205005609

EXPORT CARTON

Unit	12
Dimensions W x D x H [cm]	49 x 32 x 40
Gross weight [kg]	5.98
GTIN-13	4058205005616

PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	1 set of rechargeable batteries, USB cable
Item No.	500853
Customs tariff number	85131000
Color	black
MSRP price (€)	79.90

SINGLE PACKAGE

Dimensions W x H x D [cm]	13.5 x 11.5 x 10
Gross weight [g]	340
GTIN-13	4058205005623

INNER CARTON

Unit	6
Dimensions W x D x H [cm]	31.5 x 27.8 x 12.3
Gross weight [g]	2430
GTIN-13	4058205005630

EXPORT CARTON

Unit	12
Dimensions W x D x H [cm]	$34.5 \times 30.5 \times 27.5$
Gross weight [kg]	5.98
GTIN-13	4058205005647



4 - PRODUCT DATA SHEET v181203



ACCESORIES

PRODUCT CATEGORY	ITEM NUMBER	PRODUCT NAME	MSRP
Color filter / Signal caps	501506	Color Filter Set 36mm	19.90 €
Battery	501001	18650 Li-Ion rechargeable Battery 3400 mAh	24.90 €
Fastenings / Brackets	0359	Helmet Band Fixing Clip (4x)	6.90 €
Charger / Cable	0355	External 18650 Li-lon Charger	16.90 €



5 - PRODUCT DATA SHEET V181203



PRODUCT SERIES

The Headlamps of the Ledlenser H-Series Let somebody else do the headwork.

The "H" in H-Series stands for "head". Because with the headlamps of the H-Series everything revolves around the most important part of the body - the head. The intuitive handling, ergonomic design and the brightest LED light of this first-class headlamp ensure that you'll see more than just the light. And you can also fully rely on us for servicing.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurements according to ANSI FL1 on the respective setting. Average values, in some cases, deviations by +/- 15 % may occur due to technical reasons. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting and to battery duration (hours/hrs/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If no setting is explicitly indicated, measurement is based on "energy saving mode."

- 2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.
- 3) EP Patent 1880139, US Patent 7,461,960
- 4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the products of the "Solidline" series, Ledlenser K1 and Ledlenser K2. The warranty does not apply to defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 7, 42699 Solingen, Germany. More information: ledlenser.com/warranty
- 5) Charging time varies by hardware used.

