



— PRODUCT DATA SHEET

P3



P3

PRODUCT DESCRIPTION

The Ledlenser P3 is the big brother of the P2. With its larger head diameter of 19 mm it has a greater lighting range. But with a longer battery life of up to 6 hours¹, it is more impressive than the former P3AFSP. And when you consider its small size and light weight, up to 16 lm¹ illumination is an amazing achievement for a keychain light.

- Good lighting performance for size and weight – Up to 60 meters¹ with up to 25 lumen¹ of luminous flux
- From the homogeneous circle of close range lighting (defocused) to a sharply bundled long-distance beam (focused) – The patented³ Advanced Focus System with reflector lense enables efficient, tailored lighting
- Fast changing of the light cone with just one hand – Rapid Focus
- Keyring flashlight always to hand – Use the practical clip to attach to a shirt or coat pocket or the useful ring to attach to your keys
- Optimized operating time– 6 hours¹ in the lowest setting



TECHNICAL DATA

Length defocused [mm]	90
Length focused [mm]	93
Head diameter [mm]	19
Tube diameter [mm]	15
Weight incl. batteries [g]	35
Weight without batteries [g]	22
Focus function	Yes
Head material	Aluminum alloy
Tube material	Aluminum alloy
Optic	Plastic lense (PMMA)
Cartridge	No

POWER SUPPLY

Power source type	Battery
Battery quantity	1
Battery type	Alkaline
Battery description	Micro (AAA) 1.5V
Rechargeable	No
Energy modes	Energy Saving
Usable batteries	AAA NiMH 1.2V

FURTHER SPECIFICATIONS

IP class	IPX4
Drop test (drop height) [m]	1
Working temperature range [°C]	-20 to +40

LIGHT FUNCTIONS

Power

LIGHT SOURCE

Amount LEDs	1
LED type	Power LED
Color	White
Color temperature [K]	5500 to 9000
Color rendering index (CRI)	80

LIGHT VALUES

ANSI – Energy Saving	Boost	Power	Mid Power	Low Power
Light output ¹ [lm]		25		
Beam distance ¹ [m]		60		
Run time ¹ [h]		6		

SWITCH

End Cap Switch

TECHNOLOGIES

Advanced Focus System³, Rapid Focus

P3

PACKAGING AND LOGISTICS



Exemplary Packaging Illustration

PACKAGING INFORMATION

Type of packaging	Gift Box
Scope of delivery	1 set of batteries, Hand strap, Keyring, Pocket clip, Pouch
Item No.	500882
Customs tariff number	85131000
Color	black
MSRP price (€)	14.90

SINGLE PACKAGE

Dimensions W x H x D [cm]	14.8 x 5 x 6
Gross weight [g]	121
GTIN-13	4058205009393

INNER CARTON

Unit	6
Dimensions W x D x H [cm]	19.2 x 15.4 x 11.9
Gross weight [g]	854
GTIN-13	4058205009409

EXPORT CARTON

Unit	72
Dimensions W x D x H [cm]	40.5 x 33 x 39
Gross weight [kg]	11.238
GTIN-13	4058205009416



Exemplary Packaging Illustration

PACKAGING INFORMATION

Type of packaging	Test It Blister
Scope of delivery	2 sets of batteries, Hand strap, Keyring, Pocket clip, Pouch
Item No.	500883
Customs tariff number	85131000
Color	black
MSRP price (€)	14.90

SINGLE PACKAGE

Dimensions W x H x D [cm]	11.2 x 20.5 x 6.1
Gross weight [g]	154
GTIN-13	4058205009423

INNER CARTON

Unit	6
Dimensions W x D x H [cm]	47.2 x 21.3 x 12.5
Gross weight [g]	1239
GTIN-13	4058205009430

EXPORT CARTON

Unit	24
Dimensions W x D x H [cm]	49 x 45 x 28
Gross weight [kg]	6.186
GTIN-13	4058205009447

P3

ACCESORIES

PRODUCT CATEGORY	ITEM NUMBER	PRODUCT NAME	MSRP
Battery	500981	4x AAA Alkaline Ionic	3.49 €

P3

PRODUCT SERIES

The Ledlenser P-Series

Minimalist design, maximum performance.

The sturdy flashlights of the Ledlenser P-Series offer top performance in stylish designs. While externally they only have the bare essentials, they are packed full of useful technical functions, like the Rapid Focus and the Advanced Focus System. This makes them dependable companions for all outdoors fans and indispensable little helpers for everyday life: For example, for renovating, tidying and rearranging, taking the dog out, during blackouts, and much more.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurements according to ANSI FL1 on the respective setting. Average values, in some cases, deviations by +/- 15 % may occur due to technical reasons. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting and to battery duration (hours/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If no setting is explicitly indicated, measurement is based on "energy saving mode."

3) EP Patent 1880139, US Patent 7,461,960

4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the products of the "Solidline" series, Ledlenser K1 and Ledlenser K2. The warranty does not apply to defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 - 7, 42699 Solingen, Germany. More information: ledlenser.com/warranty