

PRODUCT DATA SHEET T7.2





2 - PRODUCT DATA SHEET v181203

T7.2

PRODUCT DESCRIPTION

What's impressive about the Ledlenser T7.2 is its even, ultra-light beam of light - on the lowest setting it can even last 25 full hours¹. You can also focus it steplessly, and locking it in place is as easy as pie. Either with your left. Or your right hand. In any case, you only need one. It will therefore never fail you or leave you in the dark.

- Good lighting performance Up to 320 lumen¹ of luminous flux with up to 260 meters¹ beam distance
- Safe handling Special, non-slip surface structure and matte Frozen Black coating make the lamp particularly easy to grip
- Optimized operational time Up to 25 hours¹ in the lowest setting
- From the homogeneous circle of close range lighting (defocused) to a sharply bundled long-distance beam (focused) – The patented³ Advanced Focus System with reflector lense enables efficient, tailored lighting
- Quick modification of the light cone with just one hand Rapid Focus with Focus Lock



TECHNICAL DATA	
Length defocused [mm]	130
Length focused [mm]	139
Head diameter [mm]	37
Weight incl. batteries [g]	175
Weight without batteries [g]	132
Focus function	Yes
Head material	Aluminum alloy
Tube material	Aluminum alloy
Optic	Plastic lense (PMMA)
Cartridge	Yes

POWER SUPPLY	
Power source type	Battery
Battery quantity	4
Battery type	Alkaline
Battery description	Micro (AAA) 1.5V
Rechargeable	No
Energy modes	Energy Saving
Usable batteries	AAA NiMH 1.2V

FURTHER SPECIFICATIONS		
IP class	IPX4	
Drop test (drop height) [m]	1	
Working temperature range [°C]	-20 to +40	

LIGHT FUNCTIONS

Low Power, Power, Boost

LIGHT SOURCE	
Amount LEDs	1
LED type	High Power LED
Color	White
Color temperature [K]	6000 to 8000
Color rendering index (CRI)	70

LIGHT VALUES	5		
ANSI – Energy Saving	Boost	Power	Mid Power Low Power
Light output ¹ [lm]	320	250	40
Beam distance ¹ [m]	260	220	100
Run time ¹ [h]	1	2	25

SWITCH

End Cap Switch

FEATURES

Focus lock

TECHNOLOGIES

Advanced Focus System³, Rapid Focus





PACKAGING INFORMATION		
Type of packaging	Gift Box	
Scope of delivery	1 set of batteries, Hand strap, Pouch.	
	Snap hook	
Item No.	9807	
Customs tariff number	85131000	
Color	black	
MSRP price (€)	74.90	

SINGLE PACKAGE	
Dimensions W x H x D [cm]	15.4 x 7.3 x 7.5
Gross weight [g]	340
GTIN-13	4029113980708

INNER CARTON	
Unit	6
Dimensions W x D x H [cm]	23.9 x 17 x 15.8
Gross weight [g]	2210
GTIN-13	4029113980715

EXPORT CARTON	
Unit	48
Dimensions W x D x H [cm]	50 x 36 x 35
Gross weight [kg]	18.86
GTIN-13	4029113980722

		ш
PACKAGING INFORMA	TION	
Type of packaging	Test It Blister	
Scope of delivery	2 sets of batteries,	
	Hand strap,	
	Pouch,	
	Snap hook	
Item No.	9907	
Customs tariff number	85131000	

51 black 74.90

SINGLE PACKAGE	
Dimensions W x H x D [cm]	15 x 28 x 9
Gross weight [g]	391
GTIN-13	4029113990752

MSRP price (€)

INNER CARTON	
Unit	6
Dimensions W x D x H [cm]	39.2 x 29.3 x 16.5
Gross weight [g]	2725
GTIN-13	4029113990714

EXPORT CARTON	
Unit	24
Dimensions W x D x H [cm]	59.8 x 41.1 x 36.1
Gross weight [kg]	12.4
GTIN-13	4029113990721



4 - PRODUCT DATA SHEET v181203

-77.2

ACCESORIES

PRODUCT CATEGORY	ITEM NUMBER	PRODUCT NAME	MSRP
Color filter / Signal caps	0039	Pouch with Color Filter Set	24.90 €
Pouches / Holster	0333	Pouch Type A	9.90 €
Pouches / Holster	0323	Tactical Professional Holster Type B	34.90 €
Fastenings / Brackets	0317	Intelligent Clip Type C	8.90 €
Fastenings / Brackets	0314	Magnetic Adaptor	9.90 €
Fastenings / Brackets	0362	Universal Mounting System	14.90 €
Fastenings / Brackets	7799-PT	Universal Mounting Bracket Type B	15.90 €
Color filter / Signal caps	0040-W	Signal Cone W 37mm	6.90 €
Color filter / Signal caps	0040	Signal Cone 37mm	6.90 €
Color filter / Signal caps	0313-F	Color Filter Set + 1x Rollprotection 37mm	19.90 €
Roll Protections	0313	Roll Protection 37mm	9.90 €
Roll Protections	0320	Roll Protection Ring 29,5 mm	6.90 €
Remote Switchs	0360	Remote Switch Type A	19.90 €
Battery	500981	4x AAA Alkaline Ionic	3.49 €



5 - PRODUCT DATA SHEET v181203

T7.2

PRODUCT SERIES

The Ledlenser T-Series
The best tactic is activation.

The "T" in this flashlight's name stands for "tactical" - although the word "tough" would do just as well. After all we developed this series for tough firefighting, police, rescue, security and technical emergency missions. All T models are therefore extremely robust, very powerful, functional and easy to use. The reason why hunters and anglers value these characteristics so much is just as clear as the shining bright light of the T7M in Boost Mode.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurements according to ANSI FL1 on the respective setting. Average values, in some cases, deviations by +/- 15 % may occur due to technical reasons. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting and to battery duration (hours/hrs/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If no setting is explicitly indicated, measurement is based on "energy saving mode."

3) EP Patent 1880139, US Patent 7,461,960

4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the products of the "Solidline" series, Ledlenser K1 and Ledlenser K2. The warranty does not apply to defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 - 7, 42699 Solingen, Germany. More information: ledlenser.com/warranty

