

Specification - LIFT Vertical Ergonomic Mouse for Mac

Product Information		
Component	Model Number (M/N)	Location
Mouse	MR0094	Bottom of the mouse

Product Dimensions				
Component	Height	Width	Depth	Weight
Mouse	108mm (4.2 in)	70mm (2.7 in)	71mm (2.7 in)	124g
With packaging (B2C)	147mm	77mm	875mm	—
With packaging (B2B)	117.5mm	765mm	855mm	—

General Product Specifications	
System Requirements	<ul style="list-style-type: none">• Windows• Chrome OS• Android• MacOS• iPadOS• Linux• Works with Surface
OS/Platform Support (at release)	<ul style="list-style-type: none">• Windows 7 / 10 or later• macOS 10.10 or later• Chrome OS• Linux• Android 5.0 or later• iPadOS 13.4 or later• Works with Surface
Software Support (at release)	Logi Options+

Mouse Specifications	
Connection Type	Bluetooth Low Energy Direct (3 channel) + BOLT (receiver not included in the package)

Mouse Specifications	
USB Protocol (Mezzi RCV)	USB 2.0
USB Speed (Mezzi RCV)	Full Speed
USB Data Format (Mezzi RCV)	16 bits/axis
USB Report Rate (Mezzi RCV)	1ms
BOLT Report Rate	7.5ms
Bluetooth Report Rate	7.5-11.25 ms
Microprocessor	Microprocessor: 32-bit ARM
DPI (Min/Max)	Resolution: 400 – 4,000 DPI (SW)
Sensor	Pluto One
Indicator Lights (LED)	BOTTOM: (3) Easy-Switch channel LEDs
Buttons	4 buttons + Connectivity button
Durability (button presses)	Buttons (Left / Right - silent): 5-million clicks Buttons (Wheel - middle-click silent): 1-million clicks Buttons (Forward and Backward): 500K clicks Connectivity button (host button): 3K clicks
Durability feet	Material type + KM Range, PTFE Feet: 100 km range
Gesture Support (Windows)	With software
Gesture Support (Mac)	With software
Materials used	PCR Plastic: (Kingfa65%PCR Or Wistron 85%PCR) Rubber: (TOPOLYMER A005&A030)
Other Features	SmartWheel

Mouse Specifications

Battery Details	AAx1
Battery Life (not rechargeable)	24 months
Is the battery user replaceable?	Yes
Corded or Wireless	Wireless
Wireless range	10 m