



Sample image

Order symbol: L 13

Product nbr: 3730692

Description: Window for 13 modules

Remarks: Clear cover

Including:

EAN: 6418074031686

EI. number:

- Finland: 3420119
- Denmark: 8212008009
- Sweden: 2539782

Dimensions:	Height	Width	Depth
mm:	257	108	0
inch:	10.12	4.25	0

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Temperatures:

Temperature °C (short term): -40 ... 120 °C

Temperature °C (continuous):

Temperature °F (short term): -40 ... 250 °F

Temperature °F (continuous): -40 ... 175 °F

Certificates: