

Outdoor light

L 20

EAN 4007841566814



Functional description

The L 20 outdoor SensorLight provides attractive, even illumination. With its sleek-looking design and the inviting ambience it creates, this light is the ideal choice for driveways, exterior walls or side entrances. Its modern look and generous, adjustable detection zone make it a veritable highlight on any building while also saving huge amounts of energy. Incidentally, it's so quick and easy to install. Your neighbour won't even notice.

Technical specifications

Dimensions(w x h x d):	230 x 240 x 80 mm
Voltage	230-240 V/50 Hz
Sensor type	Passive infrared
Output	60 W max. / E 27
Detection angle	180°
Tilting range	90 °
Capability of masking out individual segments	Yes
Reach	10 m max.
Time setting	8 sec. - 35 min.
Response brightness	2 - 2000 lx
Degree of protection (IP)	IP44
Protection class	II
Impact strength	IK07
Material	Plastic with stainless-steel trim panel
With lamp	No
Version	Silver