

PRODUCT DATASHEET

DP SLIM VALUE 1200 36 W 4000 K IP65 GY

DAMP PROOF SLIM VALUE | Damp-proof luminaire with slim housing



AREAS OF APPLICATION

- Industrial and storage facilities
- Car parks and underpasses
- Garages
- Workshops, assembly lines

PRODUCT BENEFITS

- Evenly distributed light
- Energy savings of up to 50 % (compared to luminaires that use fluorescent lamps)
- Very slim housing
- Easy installation as mounting brackets can be positioned freely on the luminaire
- Tool-free electrical connection due to push button connector
- 3 years guarantee
- Easy access to electrical terminal thanks end caps with clip mechanism

PRODUCT FEATURES

- High luminous efficacy: up to 110 lm/W
- Beam angle: 120°
- Type of protection: IP65



TECHNICAL DATA

Electrical data

Nominal wattage	36.00 W
Operating mode	Electronic control gear (ECG)
Nominal voltage	220...240 V
Power factor λ	≥ 0.90
Mains frequency	50/60 Hz

Luminaire control gear data

Output current	460 mA
----------------	--------

Photometrical data

Color temperature	4000 K
Luminous flux	4000 lm
Luminous efficacy	110 lm/W
Standard deviation of color matching	≤ 5 sdcn
Light color (designation)	Cool White
Color rendering index Ra	>80

Light technical data

Beam angle	120 °
------------	-------

Dimensions & weight



Length	1200 mm
Width	35.0 mm
Height	48.0 mm
Product weight	450.00 g

Colors & materials

Body material	Polycarbonate (PC)
Housing color	White
Product color	White
Cover material	Polycarbonate (PC)

Temperatures & operating conditions

Ambient temperature range	-20...40 °C
----------------------------------	-------------

Lifespan

Lifespan L70 at 25 °C	30000 h
Lifespan L80 at 25 °C	27000 h
Lifespan L90 at 25 °C	19000 h

Additional product data

Mounting type	Suspended/Surface
Mounting location	Ceiling



Capabilities

Dimmable	No
Type of connection	Screwless terminal, 2-Pole
Ball shot safe	No
LED module replaceable	Not replaceable

Certificates & standards

Protection class IK (shock resistance)	IK08
Glow Wire Test according to IEC 695-2-1	650 °C
Photobiological safety group EN62778	RG 0
Protection class	II
Type of protection	IP65
Standards	CE/CB

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Stainless steel clamps with safety screws included
- Mounting accessories included (suspension kit, theft protection kit)

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075066458	Folding carton box 1	39 mm x 1257 mm x 50 mm	533.00 g	2.45 dm ³
4058075066465	Shipping carton box 20	1271 mm x 215 mm x 226 mm	14090.00 g	61.76 dm ³
4058075066533	Folding carton box 1	39 mm x 1257 mm x 50 mm	533.00 g	2.45 dm ³
4058075066540	Shipping carton box 20	1271 mm x 215 mm x 226 mm	11230.00 g	61.76 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

► www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.