

# PRODUCT DATASHEET

## DP SLIM VALUE 1500 50 W 6500 K IP65 GY

**DAMP PROOF SLIM VALUE | Damp-proof luminaire with slim housing**

---

### AREAS OF APPLICATION

- Industrial and storage facilities
- Car parks and underpasses
- Garages
- Workshops, assembly lines



---

### PRODUCT BENEFITS

- Evenly distributed light
- Energy savings of up to 50 % (compared to luminaires that use fluorescent lamps)
- Very slim housing
- Easy installation as mounting brackets can be positioned freely on the luminaire
- Tool-free electrical connection due to push button connector
- 3 years guarantee
- Easy access to electrical terminal thanks end caps with clip mechanism

---

### PRODUCT FEATURES

- High luminous efficacy: up to 110 lm/W
- Beam angle: 120°
- Type of protection: IP65



**TECHNICAL DATA**

Electrical data

<b>Nominal wattage</b>	50.00 W
<b>Operating mode</b>	Electronic control gear (ECG)
<b>Nominal voltage</b>	220...240 V
<b>Power factor <math>\lambda</math></b>	$\geq 0.90$
<b>Mains frequency</b>	50/60 Hz

Luminaire control gear data

<b>Ouput current</b>	590 mA
----------------------	--------

Photometrical data

<b>Color temperature</b>	6500 K
<b>Luminous flux</b>	5500 lm
<b>Luminous efficacy</b>	110 lm/W
<b>Standard deviation of color matching</b>	$\leq 5$ sdc <sub>m</sub>
<b>Light color (designation)</b>	Cool Daylight
<b>Color rendering index Ra</b>	>80

Light technical data

<b>Beam angle</b>	120 °
-------------------	-------

Dimensions & weight



<b>Length</b>	1500 mm
<b>Width</b>	35.0 mm
<b>Height</b>	48.0 mm
<b>Product weight</b>	510.00 g

Colors & materials

<b>Body material</b>	Polycarbonate (PC)
<b>Housing color</b>	White
<b>Product color</b>	White
<b>Cover material</b>	Polycarbonate (PC)

### Temperatures & operating conditions

<b>Ambient temperature range</b>	-20...40 °C
----------------------------------	-------------

### Lifespan

<b>Lifespan L70 at 25 °C</b>	30000 h
<b>Lifespan L80 at 25 °C</b>	27000 h
<b>Lifespan L90 at 25 °C</b>	20000 h

### Additional product data

<b>Mounting type</b>	Suspended/Surface
<b>Mounting location</b>	Ceiling



### Capabilities

<b>Dimmable</b>	No
<b>Type of connection</b>	Screwless terminal, 2-Pole
<b>Ball shot safe</b>	No
<b>LED module replaceable</b>	Not replaceable

### Certificates & standards

<b>Protection class IK (shock resistance)</b>	IK08
<b>Glow Wire Test according to IEC 695-2-1</b>	650 °C
<b>Photobiological safety group EN62778</b>	RG 0
<b>Protection class</b>	II
<b>Type of protection</b>	IP65
<b>Standards</b>	CE/CB

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Stainless steel clamps with safety screws included
- Mounting accessories included (suspension kit, theft protection kit)

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075066519	Folding carton box 1	39 mm x 1557 mm x 50 mm	608.00 g	3.04 dm <sup>3</sup>
4058075066526	Shipping carton box 20	1571 mm x 215 mm x 226 mm	16890.00 g	76.33 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see  
 ▶ [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.