

# PRODUCT DATASHEET

## O SURFACE SQ 13 W 3000 K IP54 WT

OUTDOOR SURFACE SQUARE | Wall and ceiling luminaires with modern design in square shape



---

### AREAS OF APPLICATION

- Outdoor
- Building facades
- Gardens, balconies and other outdoor areas

---

### PRODUCT BENEFITS

- Energy-efficient thanks to LED technology
- 5 years guarantee
- Easy and quick installation
- Homogeneous light output

---

### PRODUCT FEATURES

- Bright and functional outdoor LED luminaires
- Type of protection: IP54
- Die-cast aluminum housing
- Available in two housing colors: white and dark gray
- Diffuser made of opal polycarbonate



**TECHNICAL DATA**

Electrical data

<b>Operating mode</b>	Mains voltage
<b>Mains frequency</b>	50/60 Hz
<b>Power factor <math>\lambda</math></b>	>0.5
<b>Nominal wattage</b>	13.00 W
<b>Nominal voltage</b>	220...240 V
<b>Nominal current</b>	0.063 A


Photometrical data

<b>Color temperature</b>	3000 K
<b>Luminous efficacy</b>	45 lm/W
<b>Luminous flux</b>	600 lm
<b>Light color (designation)</b>	Warm White
<b>Color rendering index Ra</b>	$\geq 80$
<b>Standard deviation of color matching</b>	<6 sdc <sub>m</sub>

Light technical data

<b>Beam angle</b>	100.00 °
-------------------	----------

— Dimensions & weight



<b>Length</b>	202.0 mm
<b>Width</b>	202.0 mm
<b>Height</b>	45.0 mm
<b>Product weight</b>	910.00 g

Colors & materials

<b>Housing color</b>	White
<b>Product color</b>	White

<b>Body material</b>	Aluminum
<b>Cover material</b>	Polycarbonate (PC)

### Temperatures & operating conditions

<b>Ambient temperature range</b>	-20...40 °C
----------------------------------	-------------

### Lifespan

<b>Number of switching cycles</b>	15000
<b>Lifespan L70 at 25 °C</b>	30000 h
<b>Lifespan L80 at 25 °C</b>	- h
<b>Lifespan L90 at 25 °C</b>	- h

### Additional product data

<b>Mounting type</b>	Surface
<b>Mounting location</b>	Ceiling / Wall



### Capabilities

<b>Dimmable</b>	No
<b>Type of connection</b>	Screw terminal, 3-Pole
<b>LED module replaceable</b>	Not replaceable

### Certificates & standards

<b>Type of protection</b>	IP54
<b>Protection class</b>	I
<b>Protection class IK (shock resistance)</b>	IK06
<b>Glow Wire Test according to IEC 695-2-1</b>	-
<b>Photobio. safety group acc. to EN62471</b>	RG 0
<b>Standards</b>	CE

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Complete mounting and connecting accessories included

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075074958	Folding carton box 1	65 mm x 237 mm x 228 mm	970.00 g	3.51 dm <sup>3</sup>
4058075074965	Shipping carton box 6	470 mm x 255 mm x 215 mm	6094.00 g	25.77 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see  
 ▶ [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.