

PRODUCT DATASHEET

DL COMFORT DN 155 18 W 3CCT IP54 WT

DOWNLIGHT COMFORT | Downlights with adjustable white light colors



AREAS OF APPLICATION

- Direct replacement for luminaires with compact fluorescent lamps
- General illumination
- Bathrooms, kitchens and sheltered outdoor areas
- Offices
- Corridors
- Foyers
- Shops
- Stairways

PRODUCT BENEFITS

- Three light color in one luminaire: Warm White, Cool White, Daylight White
- Simple installation thanks to integrated driver
- Easy installation with fast connection
- 5 years guarantee

PRODUCT FEATURES

- Three light colors selectable via slide switch
- Type of protection: IP54
- Connector box with push wire terminal for tool-free connection
- Through wiring possible



TECHNICAL DATA

Electrical data

Nominal wattage	18.00 W
Operating mode	Integrated LED driver
Nominal voltage	100...277 V
Power factor λ	>0.90
Mains frequency	50/60 Hz

Luminaire control gear data

Max. no. of lum. on circuit break. B16 A	11
Max. no. of lum. on circuit break. C10 A	8
Max. no. of lum. on circuit break. C16 A	13


Photometrical data

Color temperature	3000/4000/5700 K
Luminous flux	1040 lm@3000 K /1620 lm@4000 K/1470 lm@5700 K lm
Luminous efficacy	85 lm/W
Standard deviation of color matching	<5 sdc _m
Light color (designation)	Warm White/Cool White/Cool Daylight
Color rendering index Ra	>80

Light technical data

Beam angle	60 °
UGR lateral	<22
UGR longitudinal	<22

Dimensions & weight



Diameter	172.0 mm
Height	95.0 mm

Product weight	350.00 g
Mounting diameter	155.0 mm

Colors & materials

Body material	Aluminum
Housing color	White
Product color	White
Cover material	Polymethylmethacrylate (PMMA)

Temperatures & operating conditions

Ambient temperature range	-20...45 °C
----------------------------------	-------------

Lifespan

Lifespan L70 at 25 °C	50000 h
Lifespan L80 at 25 °C	45000 h
Lifespan L90 at 25 °C	30000 h
Number of switching cycles	50000

Additional product data

Mounting type	Recessed
Mounting location	Ceiling



Capabilities

Dimmable	Yes
Type of connection	Screwless terminal, 2-Pole
LED module replaceable	Not replaceable

Certificates & standards

Protection class IK (shock resistance)	IK03
Glow Wire Test according to IEC 695-2-1	650 °C
Photobio. safety group acc. to EN62471	RG 0
Protection class	I
Type of protection	IP54
Standards	CE/CB/ENEC/TÜV SÜD/RoHS

Light Distribution



LDC typ cone

LDC typ polar

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075104082	Folding carton box 1	195 mm x 195 mm x 140 mm	430.00 g	5.32 dm ³
4058075104099	Shipping carton box 8	410 mm x 410 mm x 300 mm	4680.00 g	50.43 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see
 ▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.