



# BRIO

4K Stream Edition



## FOR ULTRA-IMPACTFUL STREAMING.

Maximum impact – that’s what you’ll get with Logitech BRIO STREAM, whether you’re streaming on Twitch, recording for YouTube or video calling on Skype. Ultra HD 4K video captures the smallest details of your facial features and expressions. You stream fluid, hyper-fast 1080p/60fps video to match your gaming broadcast and create exciting slow-mo replays thanks to the high frame rate. Adjust the field of view to your use: from a broad 90° that includes more background to a narrow 78° that keeps the focus on you. Machine-learning software cleans up a cluttered background. BRIO STREAM is fully integrated with XSplit and includes a 12-month premium XSplit licence.

### WHAT’S IN THE BOX

- Ultra-high-definition webcam for streaming
- 1.5m USB cable
- Privacy shutter
- Removable clip
- Carrying pouch
- 12-month premium XSplit licence
- User documentation
- 2-year manufacturer’s guarantee

### FEATURES

- Ultra HD 4K captures you in superb definition and clarity
- HDR produces more vivid and accurate colours
- 1080p/60fps hyper-fast frame rate in HD
- Optimised for streaming
- Sharp and smooth video calls
- Integrated XSplit solution, including free 12-month premium licence



## PACKAGE SPECIFICATIONS

	Primary pack	Master shipper carton
Part	960-001194	n/a
Bar code	5099206075078 (EAN-13)	5099206075079 (SCC-14)
Weight	401.8 gr	3557.5 gr
Length	14 cm	28.6 cm
Width	8.2 cm	17 cm
Height/depth	13.7 cm	28.3 cm
Volume	1.572 dm <sup>3</sup>	0.013 m <sup>3</sup>
1 primary pack	1	n/a
1 intermediate pack	0	n/a
1 master shipper carton	8	1
1 pallet EURO	760	95
1 container 20 ft	17216	2152
1 container 40 ft	35648	4456
1 container 40 ft HQ	40104	5013

## SYSTEM REQUIREMENTS

- Windows® 8, or Windows® 10 or above with 3rd Gen Intel Core i5 or better (CPU/AVX and GPU/OpenCL support)
- Mac OS X 10.12 and above
- USB 3.0 (USB 2.0 limited to 1080p/30fps)
- Windows Hello only supported on Windows® 10 or above.

## TECHNICAL SPECS

### VIDEO RESOLUTIONS (MJPEG):

- 4K Ultra HD (up to 4096 x 2160 pixels @ 30 or 24 fps)
- 2K WQHD (up to 2560 x 1440 pixels @ 30 or 24 fps)
- 1080p Full HD (up to 1920 x 1080 pixels @ 60, 30, or 24 fps)
- 720p HD (up to 1280 x 720 pixels @ 90, 60, 30 or 24 fps)

## TECHNICAL SPECIFICATIONS:

- 13 Mpx sensor with dual core video processor
- 4K2K glass lens (F#2.0 - 4PIG)
- Autofocus from 10 cm to infinity
- 90°-78°-65° degree field of view (FOV)
- Dual 16bits omnidirectional mics with noise cancellation
- Infrared sensor technology for Windows Hello (Windows® 10 or above)
- USB 3.0 connectivity with 1.5m detachable cable (USB 2.0 limited to 1080p/30fps)
- Tripod-ready mounting system
- External privacy shutter
- Removable clip
- Carrying pouch
- 12-month premium XSplit licence

