

MC0114031-A / MC0114031-SMA-A

Portable antenna GSM 900/1800 MHz

GSM/ISM

Technical Data:

Frequency:	824-960 MHz 1710-1990 MHz
Gain:	2 dBi
Impedanz:	50 Ω
VSWR:	$\leq 2.0:1$
Polarization:	Vertikal
Specials:	2-way breakable
Connector:	SMA male (MC0114031-SMA-A) = Picture left FME female (MC0114031-A) = Picture right

