LED machine luminaire

SPOT LED 003 - MCXFL 3 S 112459006-00087899





fitted with

work equipment connected load power consumption system of protection class of protection technology usage luminaire body lamp cover

weight (net) mains lead fastening

balance of articulation joints

accessory special features

3 x Light-emitting diode

400 lumens without 24 V; AC/DC approx. 6 W IP 67

switchable remotely

external

aluminium, anodized, black

glass screen friction

approx. 0.7 kg (1.54 lbs)

approx. 3.0 m (9.84 ft); with free stranded wires


screw-down base

optional magnetic base, table clamp, wall bracket

Flood with 40° angle of radiation

illuminance

measuring conditions: d=50cm



luminous intensity

