

Brother MFC-J6957DW Inkjet A3 1200 x 4800 DPI Wi-Fi

Brand : Brother

Product code: MFC-J6957DWRE1

Product name : MFC-J6957DW



Brother MFC-J6957DW. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 1200 x 4800 DPI. Copying: Colour copying, Maximum copy resolution: 600 x 600 DPI. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI. Faxing: Colour faxing. Maximum ISO A-series paper size: A3. Wi-Fi. Direct printing. Product colour: Grey

Printing		Ports & interfaces	
Print technology *	Inkjet	Direct printing *	✓
Printing *	Colour printing	USB port	✓
Duplex printing *	✓	USB 2.0 ports quantity	1
Maximum resolution *	1200 x 4800 DPI	Network	
Print speed (ISO/IEC 24734) mono	21 ipm	Wi-Fi *	✓
Print speed (ISO/IEC 24734) colour	30 ipm	Ethernet LAN *	✓
Time to first page (black, normal)	4,6 s	Cabling technology	10/100Base-TX
N-in-1 print function	✓	Ethernet LAN data rates	10,100 Mbps
Secure printing	✓	Wi-Fi standards	802.11a,802.11b,802.11g,Wi-Fi 4 (802.11n)
Copying		Near Field Communication (NFC)	✓
Copying *	Colour copying	Security algorithms	64-bit WEP, 128-bit WEP, 802.1x RADIUS, APOL, EAP-FAST, EAP-MD5, EAP-TLS, EAP-TTLS, HTTPS, IPPS, IPSEC, PEAP, SMTX-AUTH, SMMV3, SSL/TLS, WPA-AES, WPA2-TKIP, WPA2-PSK, WPA2-PSK/WPS
Maximum copy resolution *	600 x 600 DPI	Mobile printing technologies	Apple AirPrint, Brother iPrint & Scan, Google Cloud Print, Mopria Print Service
Copier resize	25 - 400%	Performance	
N-in-1 copy function	✓	Internal memory *	512 MB
Scanning		Sound pressure level (printing)	50 dB
Duplex scanning *	✓	Sound pressure level (copying)	51,5 dB
Scanning *	Colour scanning	Design	
Optical scanning resolution *	1200 x 2400 DPI	Product colour *	Grey
Scanner type *	ADF scanner	Market positioning *	Business
Scan to	E-mail	Built-in display *	✓
Fax		Display diagonal	22,4 cm (8.8")
Faxing *	Colour faxing	Control type	Touch
Modem speed	33,6 Kbit/s	Colour display	✓
Features		Power	
Maximum duty cycle *	3500 pages per month	Power consumption (printing)	31 W
Number of print cartridges *	4	Power consumption (ready)	6 W
Printing colours *	Black, Cyan, Magenta, Yellow	Power consumption (sleep)	0,9 W
Page description languages	BR-Script 3, PCL 6, PDF 1.7, XPS	Power consumption (off)	0,03 W
Input & output capacity		System requirements	
Total input capacity *	500 sheets	Windows operating systems supported	Windows 10, Windows 7, Windows 8
Total output capacity *	100 sheets	Mac operating systems supported	Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina
Multi-Purpose tray	✓	Linux operating systems supported	✓
Multi-Purpose tray input capacity	100 sheets	Server operating systems supported	Windows Server 2008, Windows Server 2008 R2, Windows Server 2012, Windows Server 2012 R2, Windows Server 2016, Windows Server 2019
Auto document feeder (ADF)	✓	Weight & dimensions	
Auto document feeder (ADF) input capacity	50 sheets	Width	576 mm
Paper handling		Depth	477 mm
Maximum ISO A-series paper size *	A3	Height	445 mm
Paper tray media types *	Glossy paper, Plain paper, Recycled paper	Weight	27,5 kg
ISO A-series sizes (A0...A9) *	A3, A4, A5, A6	Packaging data	
		Package width	681 mm
		Package depth	561 mm

Paper handling		Packaging data	
Non-ISO print media sizes	Folio, Index card, Legal	Package height	563 mm
Envelopes sizes	C5,Com-10,DL,Monarch	Package weight	31,3 kg
Photo paper sizes	9x13,10x15,13x18	Packaging content	
Custom media width	105 - 297 mm	Cartridge(s) included	✓
Custom media length	148 - 431,8 mm		
Paper tray media weight	64 - 220 g/m ²		

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.