THIS IS A C.A.D. GENERATED DRAWING

DO NOT MAKE MANUAL REVISIONS TO MASTER.

BACKSHELL KIT INCLUDES:

(2)BACKSHELL HALVES (3)HOUSING SCREWS


(1)4-40 LONG THUMBSCREWS


(1)4-40 SHORT THUMBSCREWS

(1)SET OF COMPRESSION INSERTS—VARIOUS SIZES

DIAMETERS 4mm(.157"), 5mm(.167"), 7mm(.276"), 9mm(.354")







DIMENSIONS(mm/in)							
SIZE	A ±1.20	B ±1.20 ±0.047	C ±0.80 C ±0.031	D ±0.80 ±0.031	E ±0.80 ±0.031	F ±0.80 ±0.031	G ±0.80 ±0.031
9	15.0	30.8	15.0	24.4	50.8	18.0	26.2
	0.59	1.21	0.59	0.96	2.0	0.71	1.03
25	15.8	53.3	23.1	34.5	72.4	24.3	36.6
	0.62	2 10	0.91	1.36	2.85	0.96	1 44

\* UNLESS OTHERWISE SPECIFIED TOLERANCES

 $.XX \pm 0.35$ 

ON DECIMAL IS: ANGLE ± 1°

UNIT: MM

## ORDERING INFORMATON:

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6560-0501-01	MHDCMR-09-RA-K
25-WAY	6560-0501-03	MHDCMR-25-RA-K

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6561-0501-01	MHDCMR-09-RA
25-WAY	6561-0501-03	MHDCMR-25-RA

BACKSHELL: MATERIAL: PLATING: 4-40 THUMBSCREWS: HOUSING SCREWS: COMPRESSION INSERT: OPERATING TEMP: DIE CAST ZINC ALLOY NICKEL PLATED STEEL-Zn PLATED STEEL-Zn PLATED ASSUL RECOGNIZED -40°C TO+120°C

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN
JDHNNY

APPROVED
DAMIEN

DATE

02-24-13

DATE

03-10-14


MH CONNECTORS LTD.


SCALE	SHEET	OF	REV:
1:1	1 DF	1	3.0

DRAWING No MHDCMR-XX-RA-K



\* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE  $\pm$  1° ...  $\times$   $\pm$  0.20 ...  $\times$   $\times$  0.15 ...  $\times$  ...  $\times$   $\times$  0.05





POS.	Α	В	С	D	Е
15	16.33	24.99	30.80	19.28	2.29
26	24.85	33.32	39.10	27.75	2.29
44	38.38	47.04	53.00	41.30	2.29
62	54.86	63.50	69.30	57.40	2.41




Order Codes:

Socket Connector

Stamped & Formed

15-WAY	MHHDS-15-F-N-B-S
26-WAY	MHHDS-26-F-N-B-S
44-WAY	MHHDS-44-F-N-B-S
62-WAY	MHHDS-62-F-N-B-S



## Remark:

## 1.MATERIAL:

Plastic:PBT+30% G.F (UL94V-0) BLACK

Spcc shell:Spcc front shell is nickel plated back shell is nickel plated

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR	DRAWN IVEN (
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	APPROV

INTERNIT		DAIL	
IVEN Ou	08-18-22		
PPROVED		DATE	
CALE	SHEET	OF	REV:
1:1	1 OF	- 1	2.0

DATE

MH CONNECTORS, DIVISION OF EDAC

DRAWING No MHHDS-XX-F-N-B-S



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.