


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.

## BACKSHELL KIT INCLUDES:

- (2)BACKSHELL HALVES
- (1)GROMMET
- (2)JACKSCREWS
- (2)SHELLSCREWS
- (2)CLAMPSCREWS
- (1)METAL CLAMP
- (1)METAL CLAMP FLAT

















BACKSHELL MATERIAL: PLATING: GROMMET:

COLOR SCREW:

CLAMP:

OPERATING TEMP:

DIE CAST ZINC ALLOY NICKEL PLATED THERMOPLASTIC ABS NATURAL NICKEL PLATED STEEL, ZINC PLATED STEEL, SHEET, NICKEL PLATED -40°C TO +120°C

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



\* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE  $\pm$  1° UNIT: MM .XX  $\pm$  0.50

DIMENSIONS(mm/in)					
SIZE	A ±.30 ±.012	B ±.50 ±.020	C ±.25 ±.010	D ±1.3 D ±.051	E
9	41.3	15.4	24.99	32.2	13.0
9	1.626	0.606	0.984	1.268	0.512
15	43.3	15.4	33.32	40.6	13.0
15	1.705	0.606	1.312	1.598	0.512
25	49.5	15.4	47.04	54.5	13.0
20	1.949	0.606	1.852	2.146	0.512
37	54.3	15.4	63.50	70.7	13.0
57	2.138	0.606	2.500	2.783	0.512

### ORDERING INFORMATION:

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6560-0136-01	MHDM-9-K
15-WAY	6560-0136-02	MHDM-15-K
25-WAY	6560-0136-03	MHDM-25-K
37-WAY	6560-0136-04	MHDM-37-K

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN	DATE
Johnny	11-24-15
APPROVED	DATE
Victor Lin	11-24-15

MH CONNECTORS, DIVISION OF EDAC

SCALE	SHEET	OF	REV:
1:1	1 OF	<del>-</del> 1	4.0
DD AVAULUS AV			


DRAWING No MHDM-XX-K

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



\* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE X.\*  $\pm$  3' X.X\*  $\pm$  1' UNIT: MM X.  $\pm$  0.30 X.X  $\pm$  0.25


X.XX ± 0.20 X.XXX ± 0.15




# Order Codes:

Plug Connector Stamped & Formed

15-WAY	MHHDS-15-M-N-B-S
26-WAY	MHHDS-26-M-N-B-S
44-WAY	MHHDS-44-M-N-B-S
62-WAY	MHHDS-62-M-N-B-S





POS.	Α	В	С	D	E
15	16.90	24.99	30.80	19.10	2.29
26	25.30	33.32	39.10	27.75	2.29
44	39.00	47.04	53.00	41.30	2.29
62	55.40	63.50	69.30	57.40	2.41

# Remark:1.MATERIAL:

Plastic:PBT+30% G.F (UL94V-0) BLACK

Spcc shell:Spcc front shell is nickel plated back shell is nickel plated

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN	DATE
IVEN Ou	08-18-22
APPROVED	DATE

COMPLIANT

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



MH CONNECTORS, DIVISION OF EDAC

DRAWING No

MHHDS-XX-M-N-B-S