
THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



## BACKSHELL KIT INCLUDES:

- (1)BACKSHELL
- (2)4-40 THUMBSCREWS
- (1)PLASTIC STRAIN RELIEF
- (1)METAL STRAIN RELIEF CLAMP
- (2)STRAIN RELIEF SCREWS

TORQUE VALUE ON PLASTIC FOR STRAIN RELIEF SCREWS=4 INCH POUNDS MAX



DIMENSIONS(mm/in)						
SIZE	A ±:8 ±:032	B ±.3 ±.012	C ±.5 ±.02	D ±.5 ±.02	E	F ±.5 ±.02
4.5	40.00	33.32	34.00	15.00	11.50	47.20
15	1.575	1.312	1.339	0.591	0.453	1.858

ORDERING INFORMATION: (YY=COLOR)

SIZE	P/N-KITTED:	P/N-BULK:
15-WAY	MHDPPK15-YY-K	MHDPPK15-YY

COLOR CODE CHART:

BLACK = BK

LIGHT GREY = LG

DEC GREY = DE

RED = R

BLUE = BYELLOW = Y

GREEN = G

WHITE = W

MATERIAL: POLYAMIDE PA66-UL RECOGNIZED MATERIAL

SEE COLOR CODE CHART.

THUMBSCREWS: STEEL, BLACK OXIDE (FOR BLACK HOODS)

STEEL, Zn PLATED (FOR COLORED HOODS)

OPERATING TEMP: -55°C TO+110°C .



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

MH CONNECTORS, DIVISION OF EDAC

	DRAWN	DATE		
	HALE	06-2	4-15	
Т	APPROVED DAMIEN		DATE 06-3	0-15
	SCALE	SHEET	OF	REV:

1 OF 1


2.0


DRAWING No
MHDPPK15-SLIM SERIES

NTS



\* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE  $\pm$  1° ...  $\times$   $\pm$  0.20 ...  $\times$   $\times$  0.15 ...  $\times$  ...  $\times$   $\times$  0.05





POS.	Α	В	С	D	Е
15	16.33	24.99	30.80	19.28	2.29
26	24.85	33.32	39.10	27.75	2.29
44	38.38	47.04	53.00	41.30	2.29
62	54.86	63.50	69.30	57.40	2.41




Order Codes:

Socket Connector

Stamped & Formed

15-WAY	MHHDS-15-F-N-B-S
26-WAY	MHHDS-26-F-N-B-S
44-WAY	MHHDS-44-F-N-B-S
62-WAY	MHHDS-62-F-N-B-S



## Remark:

## 1.MATERIAL:

Plastic:PBT+30% G.F (UL94V-0) BLACK

Spcc shell:Spcc front shell is nickel plated back shell is nickel plated

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR	DRAWN IVEN (
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	APPROV

INTERNIT		DAIL	
IVEN Ou		08–1	8-22
PPROVED		DATE	
CALE	SHEET	OF	REV:
1:1	1 OF	- 1	2.0

DATE

MH CONNECTORS, DIVISION OF EDAC

DRAWING No MHHDS-XX-F-N-B-S



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.