THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




BACKSHELL KIT INCLUDES:


(2) BACKSHELL HALVES (2)4-40 THUMBSCREWS

(2)HOUSING SCREWS & (2)NUTS (1)SET OF COMPRESSION INSERTS-VARIOUS SIZES

DIAMETERS:4mm(.157"),5mm(.197"),7mm(.276"),9mm(.351")

NOTE: 37 POSITION HAS (4) HOUSING SCREWS & (4)NUTS





DIMENSIONS(mm/in) В С D А (±0.50) MM (± 0.50) (± 0.50) ММ (± 0.50) ΜМ MM SIZE (± 0.02) INCH (±0.02) INCH (±0.02) INCH (± 0.02) INCH ММ MM MM ММ 15.00 31.50 24.99 40.50 9 INCH INCH INCH INCH 1.240 0.984 1.594 0.591 MM 40.00 MM MM 40.50 ММ 15.00 33.32 15 INCH 1.575 INCH INCH 1.594 INCH 0.591 1.312 ΜМ ΜМ MM 54.00 MM 49.50 15.00 47.04 25 INCH INCH INCH 2.126 INCH 1.949 0.591 1.852 MM 70.50 MM MM 54.50 ΜМ 16.00 63.50 37

ORDERING INFORMATON:

2.776

INCH

INCH

ON DECIMAL IS:

SIZE	P/N – KITTED	PRODUCT CODE		
9-WAY	6560-0145-01	MHDTPK-9-K		
15-WAY	6560-0145-02	MHDTPK-15-K		
25-WAY	6560-0145-03	MHDTPK-25-K		
37-WAY	6560-0145-04	MHDTPK-37-K		

2.500

INCH

2.146

INCH

0.630

SIZE	P/N – BULK	PRODUCT CODE		
9-WAY 6561-0145-01		MHDTPK-9		
15-WAY 6561-0145-02		MHDTPK-15		
25-WAY	6561-0145-03	MHDTPK-25		
37-WAY	6561-0145-04	MHDTPK-37		

PLASTIC: ABS UL 94-HB RATED PLATING: NICKEL PLATED JACKSCREWS: STEEL-ZINC PLATED M3 HOODSCREWS: STEEL-ZINC PLATED COMPRESSION INSERTS: ABS UL 94-HB RATED M3 NUTS: STEEL-ZINC PLATED OPERATING TEMP: -55°C TO+110°C



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



THE MANUFACTURE OR SALE OF APPARATUS WITHOU WRITTEN PERMISSION. MH CONNECTORS, **DIVISION OF EDAC**

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE

REPRODUCED. COPIED OR USED AS THE BASIS FOR

	DRAWN		DATE	
	Johnny		03–1	5–22
л	APPROVED	DATE		
	Victor Lin	03–15–22		
	SCALE	SHEET	OF	REV:
		10	F 2	4.0
	DRAWING No			
	MHDTPK S	ERIES		

DRAWING UPDATED 3 Johnny DEC.04-2020 4 DRAWING UPDATED Johnny March, 15-2022


* UNLESS OTHERWISE SPECIFIED TOLERANCES


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS:


DRAWING UPDATED (3) Johnny DEC.04-2020 DRAWING UPDATED (4) Johnny March.15-2022







47.1±0.3



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

MH CONNECTORS,

DIVISION OF EDAC

	DRAWN		DATE	
	Johnny		03–1	5–22
-	APPROVED		DATE	
	Victor Lir	n	03–1	5–22
	SCALE	SHEET	OF	REV:
		2 0	F 2	4.0
	DRAWING No			
	MHDTPK S	SERIES		


-40 UNC



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



THIS IS A C.A.D. GENERATED DRAWING DD NDT MAKE MANUAL RE∨ISIDNS TD MASTER.




* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: .XX \pm 0.35

UNIT: MM

-G(MAX)

0.72



Material & Finish Shell: Steel Nickel or Tin plated

Pin Contact: Brass Gold plated over nickel

Insulator: PBT glass-fiber reinforced UL 94-V0

Number of contact: 9,15,25,37,50

Current rating: 5 amp

Dielectric strength: 1000V for one minute


Insulator resistance: 1000MΩ Min at 500V DC

Temperature:-55°C ~105°C

ITEM NO	А	В	С	D	E	F	G	н
MHDM9SP	16.92(0.666)	24.99(0.984)	30.81(1.213)	19.23(0.757)	1.0(0.0394)	10.8(0.425)	2.7(0.106)	5.84(0.23)
MHDM15SP	25.25(0.994)	33.32(1.312)	39.14(1.541)	27.56(1.085)	1.0(0.0394)	10.8(0.425)	2.7(0.106)	5.84(0.23)
MHDM25SP	38.96(1.534)	47.04(1.852)	53.04(2.088)	41.30(1.625)	1.0(0.0394)	10.8(0.425)	2.7(0.106)	5.84(0.23)
MHDM37SP	55.42(2.182)	63.50(2.500)	69.32(2.729)	57.71(2.272)	1.0(0.0394)	10.8(0.425)	2.7(0.106)	5.84(0.23)
MHDM50SP	52.86(2.081)	61.11(2.406)	66.92(2.634)	55.30(2.177)	1.0(0.0394)	10.8(0.425)	2.7(0.106)	5.84(0.23)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

MH CONNECTORS LTD.



MHDM SP

DATE

DATE

07-24-12



