

* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS:

DRAWING UPDATED 3
Johnny DEC.04-2020


DRAWING UPDATED 4
Johnny March.15-2022


BACKSHELL KIT INCLUDES:

- (2)BACKSHELL HALVES
- (2)4-40 THUMBSCREWS
- (2)HOUSING SCREWS & (2)NUTS
- (1)SET OF COMPRESSION INSERTS-VARIOUS SIZES DIAMETERS:4mm(.157"),5mm(.197"),7mm(.276"),9mm(.351")

NOTE: 37 POSITION HAS (4) HOUSING

SCREWS & (4)NUTS





DIMENSIONS(mm/in)								
		A	В С		С	D		
	ММ	(±0.50)	ММ	(±0.50)	ММ	(±0.50)	ММ	(±0.50)
SIZE	INCH	(±0.02)	INCH	(±0.02)	INCH	(±0.02)	INCH	(±0.02)
9	ММ	31.50	ММ	24.99	ММ	40.50	ММ	15.00
9	INCH	1.240	INCH	0.984	INCH	1.594	INCH	0.591
4.5	ММ	40.00	ММ	33.32	ММ	40.50	ММ	15.00
15	INCH	1.575	INCH	1.312	INCH	1.594	INCH	0.591
25	ММ	54.00	ММ	47.04	ММ	49.50	ММ	15.00
	INCH	2.126	INCH	1.852	INCH	1.949	INCH	0.591
37	ММ	70.50	ММ	63.50	ММ	54.50	ММ	16.00
37	INCH	2.776	INCH	2.500	INCH	2.146	INCH	0.630

ORDERING INFORMATON:

SIZE	P/N – KITTED	PRODUCT CODE
9-WAY	6560-0145-01	MHDTPK-9-K
15-WAY	6560-0145-02	MHDTPK-15-K
25-WAY	6560-0145-03	MHDTPK-25-K
37-WAY	6560-0145-04	MHDTPK-37-K

SIZE	P/N - BULK	PRODUCT CODE
9-WAY	6561-0145-01	MHDTPK-9
15-WAY	6561-0145-02	MHDTPK-15
25-WAY	6561-0145-03	MHDTPK-25
37-WAY	6561-0145-04	MHDTPK-37

DRAWN

PLASTIC: ABS UL 94-HB RATED PLATING: NICKEL PLATED

JACKSCREWS: STEEL-ZINC PLATED M3 HOODSCREWS: STEEL-ZINC PLATED

COMPRESSION INSERTS: ABS UL 94-HB RATED

M3 NUTS: STEEL-ZINC PLATED OPERATING TEMP: -55°C TO+110°C



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

 Johnny
 03–15–22

 APPROVED Victor Lin
 DATE 03–15–22

 SCALE SHEET OF REV.

DATE

MH CONNECTORS, DIVISION OF EDAC


MHDTPK SERIES





* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS:


DRAWING UPDATED 3
Johnny DEC.04-2020

DRAWING UPDATED 4
Johnny March.15-2022









R S COMPLIANT

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.



MH CONNECTORS, DIVISION OF EDAC

THESE DRAWINGS AND SPECIFICATIONS ARE THE

PROPERTY OF MH CONNECTORS AND SHALL NOT BE

REPRODUCED, COPIED OR USED AS THE BASIS FOR

WRITTEN PERMISSION.


THE MANUFACTURE OR SALE OF APPARATUS WITHOUT


SCALE SHEET OF REV: 2 OF 2 4.0

DRAWING No
MHDTPK SERIES



* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE \pm 1° ... \times \pm 0.20 ... \times \times 0.15 ... \times ... \times \times 0.05





POS.	Α	В	С	D	Е
15	16.33	24.99	30.80	19.28	2.29
26	24.85	33.32	39.10	27.75	2.29
44	38.38	47.04	53.00	41.30	2.29
62	54.86	63.50	69.30	57.40	2.41




Order Codes:

Socket Connector

Stamped & Formed

15-WAY	MHHDS-15-F-N-B-S
26-WAY	MHHDS-26-F-N-B-S
44-WAY	MHHDS-44-F-N-B-S
62-WAY	MHHDS-62-F-N-B-S



Remark:

1.MATERIAL:

Plastic:PBT+30% G.F (UL94V-0) BLACK

Spcc shell:Spcc front shell is nickel plated back shell is nickel plated

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR	DRAWN IVEN (
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	APPROV

TATIVITY		DAIL	
IVEN Ou	08-18-22		
PPROVED		DATE	
CALE	SHEET	OF	REV:
1:1	1 OF	- 1	2.0

DATE

MH CONNECTORS, DIVISION OF EDAC

DRAWING No MHHDS-XX-F-N-B-S



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.