




DO NOT MAKE MANUAL REVISIONS TO MASTER.


## BACKSHELL KIT INCLUDES:

- (2)BACKSHELL HALVES
- (2)4-40 THUMBSCREWS
- (2)HOUSING SCREWS
- (1)SET OF COMPRESSION INSERTS-VARIOUS SIZES FOR 9-37 DIAMETERS 4mm(.157"), 5mm(.167"), 7mm(.276"), 9mm(.354")
- (1)SET OF COMPRESSION INSERTS-VARIOUS SIZES FOR 50 DIAMETERS 11mm(.433"), 12.5mm(.492"), 14mm(.551"), 15mm(.591")













PLATING: JACKSCREWS: STEEL: ZN PLATED WITH PLASTIC KNOB

STEEL:ZN PLATED M3 HOODSCREWS: COMPRESSION INSERT: ABS,UL RECOGNIZED OPERATING TEMP: -40°C TO+120°C



THIS SERIES FULLY CONFORMS TO THE **EUROPEAN UNION DIRECTIVES 2002/95/EC** AND 2002/96/EC FOR RoHS COMPLIANCY.



#### \* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE ± 1° $.XX \pm 0.35$ UNIT: MM

DIMENSIONS(mm/in)						
SIZE A ±50,02 B ±50,02 C ±50,02 D ±						
9	31.20	39.90	15.00	24.99		
	1.228	1.571	0.591	0.984		
15	39.50	41.50	15.00	33.32		
15	1.555	1.634	0.591	1.312		
25	53.40	48.60	15.00	47.04		
20	2.102	1.913	0.591	1.852		
37	69.70	53.60	15.00	63.50		
	2.744	2.110	0.591	2.500		
50	67.50	54.00	18.70	61.00		
30	2.657	2.126	0.736	2.402		

### ORDERING INFORMATON:

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6560-3105-01	MHDTZK-09-RA-PC-K
15-WAY	6560-3105-02	MHDTZK-15-RA-PC-K
25-WAY	6560-3105-03	MHDTZK-25-RA-PC-K
37-WAY	6560-3105-04	MHDTZK-37-RA-PC-K
50-WAY	6560-3105-05	MHDTZK-50-RA-PC-K

SIZE	P/N - BULK	PRODUCT CODE
9-WAY	6561-3105-01	MHDTZK-09-RA-PC
15-WAY	6561-3105-02	MHDTZK-15-RA-PC
25-WAY	6561-3105-03	MHDTZK-25-RA-PC
37-WAY	6561-3105-04	MHDTZK-37-RA-PC
50-WAY	6561-3105-05	MHDTZK-50-RA-PC

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

١	DRAWN	DATE
	Johnny	11-24-15
	APPROVED	DATE
	Victor Lin	11-24-15




MH CONNECTORS, **DIVISION OF EDAC** 


SCALE	SHEET	OF	REV:
1:1	1 OF	- 1	7.0
DRAWING No			

MHDTZK-RA-PC



\* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS: ANGLE  $\pm$  1° ...  $\times$   $\pm$  0.20 ...  $\times$   $\times$  0.15 ...  $\times$  ...  $\times$   $\times$  0.05





POS.	Α	В	С	D	Е
15	16.33	24.99	30.80	19.28	2.29
26	24.85	33.32	39.10	27.75	2.29
44	38.38	47.04	53.00	41.30	2.29
62	54.86	63.50	69.30	57.40	2.41




Order Codes:

Socket Connector

Stamped & Formed

15-WAY	MHHDS-15-F-N-B-S
26-WAY	MHHDS-26-F-N-B-S
44-WAY	MHHDS-44-F-N-B-S
62-WAY	MHHDS-62-F-N-B-S



# Remark:

# 1.MATERIAL:

Plastic:PBT+30% G.F (UL94V-0) BLACK

Spcc shell:Spcc front shell is nickel plated back shell is nickel plated

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF MH CONNECTORS AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR	DRAWN IVEN (
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	APPROV

INTERNIT		DAIL	
IVEN Ou		08–1	8-22
PPROVED		DATE	
CALE	SHEET	OF	REV:
1:1	1 OF	- 1	2.0

DATE

MH CONNECTORS, DIVISION OF EDAC

DRAWING No MHHDS-XX-F-N-B-S



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2002/95/EC AND 2002/96/EC FOR RoHS COMPLIANCY.