




MKL 0,64/25-0,25 schwarz/black

Measuring and Testing Equipment:Measuring leads:0,64 mm system

Description	Measuring lead with two insulated sockets for 0.64 mm round pillar and 0.64 mm rectangular pillar. Highly flexible 0.25 mm two stranded wire with two 0.64 mm diameter sockets.
Type	MKL 0,64/25-0,25 schwarz/black
Order No.	973 604-100
System	0.64 mm system
Cable length	25 cm
Conductor size	0,25 mm²
Cable material	PVC
Cable color	black
Housing Color	black
Other standard types	red color,wert=



Technical data		
Pin dimensions	0,64 mm	
Type of contact	socket (spring loaded)	
Type of termination	0,64 mm diameter socket	
Cable type	LIY	
Cable specification	highly flexible lead	
Wire stranding	130 mm x 0,05 mm	
Rated voltage	DC 60 V	
Rated current	3 A	
Contact resistance	20 mOhm	
Material		

Housing material
Environmental conditions
Temperature range PVC

-40 °C to +60 °C