

# X1128H DLP Projector

---

Model: X1128H

Part: MR.JTG11.001

Acer Essential series projectors are best value projectors ideal for everyday use, at work or home. Make your presentations more compelling and entertainment more exciting with high brightness, high contrast and DLP® 3D Ready2, while adhering to your bottom line.

## [Overview](#) [Tech Specs](#) [Support](#)

### Native Resolution

800 x 600

### Maximum Resolution

1920 x 1200

### Standard Mode Brightness

4800 lm

### Native Aspect Ratio

4:3

### Compatible Aspect Ratio

16:9

### Contrast Ratio

20,000:1

### Throw Ratio

1.94 to 2.16 (1295.40 mm@2000 mm)

### Digital Zoom

2x

### Vertical Keystone Correction

-40°/+40°

### Maximum Vertical Sync

120 Hz

Maximum Horizontal Sync

100 kHz

Minimum Vertical Sync

24 Hz

Minimum Horizontal Sync

15 kHz

Colour Supported

1.07 Billion Colors (30-bit)

Lamp

Number of Lamps

1

Lamp Power

220 W

Normal Mode Lamp Life

6000 Hour

Economy Mode Lamp Life

10000 Hour

ExtremeEco Mode Lamp Life

15000 Hour

Interfaces/Ports

Number of USB Ports

1

USB

Yes

USB Connector Type

1 x Type-A

Composite Video

Yes

Number of VGA Inputs

1

VGA In

Yes

Number of VGA Outputs

1

VGA Out

Yes

Number Of Audio Inputs

1

Number Of Audio Outputs

1

Audio Line In

Yes

Audio Line Out

Yes

Technical Information

Projection System

DLP

Projection Method

- Front
- Rear
- Ceiling
- Rear Ceiling

Video Compatibility

- NTSC
- PAL
- SECAM

- HDTV
- EDTV
- SDTV

#### Computer Compatibility

- Windows PC
- Mac PC

#### Audio

##### Number of Speakers

1

##### Speaker Output Power

3 W

##### Speaker Output Mode

Mono

#### Power Description

##### Power Supply

100 V AC ~ 240 V AC

##### Input Voltage

- 120 V AC
- 230 V AC

##### Operating Power Consumption

275 W

##### Standby Power Consumption

500 mW

#### Physical Characteristics

##### Fan Noise

- 32 dB Approximate Standard Mode
- 24 dB Approximate Economy Mode

##### Weight (Approximate)

2.80 kg

## Form Factor

Ceiling Mountable

## Height

113.7 mm

## Width

313 mm

## Depth

240 mm

## Miscellaneous

### Optional Accessories

- Carrying Case (MC.JPV11.005)
- 3D Glasses (MC.JFZ11.00B)
- Lamp (MC.JR711.008)
- WirelessCAST (MWA3) (MC.JKY11.007)
- Ceiling Mount (MC.JLC11.003)

<sup>[1]</sup>Specifications vary depending on model and/or region.