

BRIGHT, CLEAR, AND WIRELESS





Acer X1328Wi

Wireless Projection WXGA (1,280 x 800) 4,500 ANSI lumens 24/7 operation

Product Specifications

Model name	X1328Wi
Projection system	DLP®
Resolution	WXGA(1,280 x 800) Maximum WUXGA (1,920 x 1,200)
Brightness	4,500 ANSI Lumens (Standard), 3,600 ANSI Lumens (ECO),(Compliant with ISO 21118 standard)
Aspect ratio	16:10 (Native), 4:3/16:9 (Supported)
Contrast ratio	20,000:1Dynamic Black
Throw ratio	1.54~1.72 (60"@2m)
Zoom ratio	1.1X
Projection lens	F= 2.41~2.53, f = 21.85~24.00mm Manual Zoom & Focus
Lamp life	6,000 Hours (Standard), 10,000 Hours (ECO), 15,000 Hours (ExtremeEco)
Noise level	27 dBA (ECO)
Input interface	Analog RGB/Component Video (D-sub) x 1 HDMI (Video, Audio, HDCP) x 1 PC Audio (Stereo mini jack) x 1 Composite Video (RCA) x 1 USB (Type A) x 1, for wireless dongle
Output interface	DC Out (5V/1A, USB Type A) x 1 PC Audio (Stereo mini jack) x 1
Control interface	RS232 (D-sub) x 1
Dimensions	313 x 240 x 113.7mm (12.3" x 9.4" x 4.5")
Weight	2.75kg (6.06lb)

Product View

Acer EcoProjection reduces power consumption up to (ExtremeEco mode) X1328Wi Part Number: MR.JTW11.001 EAN Code: 4710886243298 Control panel Focus ring DC 5V Composite Video Zoom ring Lamp cover WirelessKit HDMI Audio in Lens Standard Accessory **Optional Accessory** Audio out Power socket RS232

Ceiling Mount

CM-01S



Wireless

UWA5

Projection-Kit

Superior Laser Lighting

4,500 lumens high brightness provides the ability to project crystal clear, vibrant images from a long distance on a large screen even in daytime indoors.



Ceiling Mount

CM-02S

BlueliahtShield™


3D Glasses

E4W



Wireless Projection

Paring with default Acer wireless dongle1, you will be able to skip the cable and project from your smartphone, laptop or PC via wireless signal. Screen Mirroring2 support allows quick and seamless screenmirroring without installing extra app.



Additional device must support Miracast technology.



Acer LumiSense

light and protect your eyes.

Acer BluelightShield

LumiSense incorporates a clever content-aware process. It analyzes projected content frame by frame and dynamically adjusts image visibility to optimum levels. Thanks to LumiSense intelligent judgment and dynamic adjustment, all dark scenes are clearly displayed with no loss of detail.

Acer Bluelightshield allows users to lower levels of blue light to

lessen the $\overset{-}{\text{negative}}$ effects of blue light exposure. There are three

levels of filter in projector suitable for different scenario. Each level

also contains dynamic mechanism that will optimize the blue light level based on content. Bluelightshield can reduces up to 30% blue

About Acer

Wireless Projection





Feature Highlights **Expressive Display**

- 4,500 lumens high brightness
- 20,000:1 Dynamic Black
- Acer LumiSense smart adjustment
- Acer Bluelight Shield
- Acer ColorBoost3D brings true-to-life color
- Acer ColorSafe II prevents color decay
- HDMI3D

Enhanced Usability

- Wireless projection frees you from cable chaos (default)
- Hidden dongle design
- 3W built-in speaker
- 24/7 operation

Installation flexibility

- +/-40° (Vertical, Manual & Auto) KeystoneAuto ceilingmounted correction
- AC power on
- I/O power on

Eco-friendly Functionality

- Up to 15,000 hours lamp life