

X1526HK DLP Projector

Model: X1526HK

Part: MR.JV611.001

Enjoy brilliant visuals and flexible installation with an Acer X1526HK projector. With FHD resolution, 4,000 lumens, and color-enhancing technologies, you'll optimize meetings and boost productivity at the same time.

[Overview](#) [Tech Specs](#) [Support](#)

Image

Native Resolution

1920 x 1080

Maximum Resolution

1920 x 1200

Standard Mode Brightness

4000 lm

Native Aspect Ratio

16:9

Compatible Aspect Ratio

4:3

Contrast Ratio

10,000:1

Digital Zoom

2x

Vertical Keystone Correction

-40°/+40°

Maximum Vertical Sync

120 Hz

Maximum Horizontal Sync

100 kHz

Minimum Vertical Sync

24 Hz

Minimum Horizontal Sync

15 kHz

Colour Supported

1.07 Billion Colors (30-bit)

Lamp

Lamp Type

OSRAM

Number of Lamps

1

Lamp Power

245 W

Interfaces/Ports

Number Of Audio Inputs

1

Number Of Audio Outputs

1

Audio Line In

Yes

Audio Line Out

Yes

Technical Information

Projection System

DLP

Projection Method

- Front
- Rear
- Ceiling
- Rear Ceiling

Video Compatibility

- NTSC
- PAL
- SECAM
- HDTV
- EDTV
- SDTV

Computer Compatibility

- Windows PC
- Mac PC
- Google Chrome PC

Audio

Number of Speakers

1

Speaker Output Power

3 W

Speaker Output Mode

Mono

Power Description

Input Voltage

- 120 V AC
- 230 V AC

Operating Power Consumption

290 W

Standby Power Consumption

500 mW

Physical Characteristics

Installation

Ceiling Mount

Weight (Approximate)

2.60 kg

Form Factor

Ceiling Mountable

Height

91 mm

Width

322 mm

Depth

225 mm

Miscellaneous

Package Contents

- X1526HK DLP Projector
- AC Power Cord
- Battery for remote control
- Quick Start Guide
- Remote Control

Optional Accessories

Lamp (UC.JT211.001)

[1]Optional 3D glasses are required.

[2]Supports up to 1080p resolution.

[3]Projector operation varies depending on product configuration, power settings and usage, among other factors.