

# X1528Ki DLP Projector

---

[acer.com/gb-en/projectors/meeting-room/pdp/MR.JW011.001](http://acer.com/gb-en/projectors/meeting-room/pdp/MR.JW011.001)

Model: X1528Ki

Part: MR.JW011.001

With 5,200 lumens of brightness and FHD (1920 X 1080) resolution, the Acer X1528Ki projector delivers bright and clear images even in well-lit rooms. It also features Acer LumiSense™, ColorBoost3D™, and ColorSafe II so that you can enjoy true-to-life color.

[Overview](#) [Tech Specs](#) [Support](#)

Image

Native Resolution

1920 x 1080

Maximum Resolution

1920 x 1200

Standard Mode Brightness

5200 lm

Native Aspect Ratio

16:9

Compatible Aspect Ratio

4:3

Contrast Ratio

10,000:1

Digital Zoom

2x

Vertical Keystone Correction

-40°/+40°

Maximum Vertical Sync

120 Hz

Maximum Horizontal Sync

100 kHz

Minimum Vertical Sync

24 Hz

Minimum Horizontal Sync

15 kHz

Colour Supported

1.07 Billion Colors (30-bit)

Lamp

Number of Lamps

1

Lamp Power

245 W

Interfaces/Ports

USB

Yes

Number Of Audio Inputs

1

Number Of Audio Outputs

1

Audio Line In

Yes

Audio Line Out

Yes

Technical Information

Projection System

DLP

Projection Method

- Front
- Rear
- Ceiling
- Rear Ceiling

#### Video Compatibility

- NTSC
- PAL
- SECAM
- HDTV
- EDTV
- SDTV

#### Computer Compatibility

- Windows PC
- Mac PC
- Google Chrome PC

#### Audio

##### Number of Speakers

1

##### Speaker Output Power

3 W

##### Speaker Output Mode

Mono

#### Network & Communication

##### Wireless Capability

- EZCast
- Miracast Wi-Fi

#### Power Description

##### Operating Power Consumption

290 W

##### Standby Power Consumption

500 mW

#### Physical Characteristics

## Installation

Ceiling Mount

## Weight (Approximate)

2.95 kg

## Form Factor

Ceiling Mountable

## Height

4.2 mm

## Width

12.3 mm

## Depth

10 mm

## Miscellaneous

### Package Contents

- X1528Ki DLP Projector
- AC Power Cord
- Battery for remote control
- Lens Cap
- Quick Start Guide
- Remote Control
- Security Card
- VGA Cable

### Optional Accessories

- 3D Glasses (MC.JFZ11.00B)
- Lamp (MC.JS411.002)
- Ceiling Mount (MC.JLC11.003)

[1]Projector operation varies depending on product configuration, power settings and usage, among other factors.

[2]Specifications vary depending on model and/or region.

[3]Additional apps may be required to access wireless projection features.

