



Portable SSD MS60

Discover Future-Forward SSD



The MS60 is a stick-style SSD that offers superior transfer speeds compared to traditional USB 2.0. It enables the immediate and smooth transfer of images, videos, and files between devices. This lightweight device is an ideal solution for creative individuals, allowing them to concentrate more on their creative process.



High-speed Transfers



Ample capacity



SP Widget Software

Features

- USB 3.2 Gen 2 for high-speed data transfers
- Ample capacity of up to 1TB
- Comes with free SP Widget software for backup, restore, AES 256-bit encryption, and cloud storage
- Impressive read speeds of up to 600MB/s and write speeds of up to 500MB/s
- Sturdy metal housing featuring a convenient flip cap design
- Easy Plug & Play use
- Includes Recuva File Recovery for effortless file retrieval

Specifications

Capacity	250GB, 500GB, 1TB
Dimensions	71.3 x 21.3 x 10.4mm
Weight	13.8g
Material	Aluminum + Rubber
Color	Blue
Sequential Read/Write (max.)	Up to 600/500MB/s
Interface	USB Type-A 3.2 Gen 2 (USB 3.1 Gen 2, USB 3.1 Gen 1 & USB 3.0 & USB 2.0 backwards-compatible)
OS Compatibility	PC- Windows 11/10/8.1/8/7/Vista/XP, Mac OS 10.3.x or later, Linux 2.6.x or later Mobile device- Android 6.0.X* or later / iOS 13 or later
Operating Temperature	0°C - 70°C
Certification	CE, UKCA, FCC, BSMI
Warranty	5-year limited warranty

Ordering Information

Capacity	Part Number
250GB	SP250GBUF3S60V1B
500GB	SP500GBUF3S60V1B
1TB	SP001TBUF3S60V1B

