Amphenol

M SERIES (MUSICIAN RANGE)



Features:

- Mono or Stereo (TRS).
- Stylish shell design.
- · Robust diecast shell in Satin nickel or Black finish.
- Nickel or Gold contact plating.Flexible grommet cable protection.
- · Improved solderability.
- Precision machined contacts.
- · Standard or Bulk packaging.
- Cable OD Entry to 6.5mm (0.256")

Options: Black Shell, Gold contacts. Coloured grommets (ordered separately)

Specifications: Page 109

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
	₩	79 [3.115"]———————————————————————————————————	1/4" (6.35mmø) Mono Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPM-GN
				Gold Plated Contacts	ACPM-GN-AU
				Bulk Pack	ACPM-GN BULK
	49 [1.922"] Mono Phone I Diecast Shell, Black finish,	,	Standard	ACPM-GB	
a de la companya de l		Amphenol	Flexible grommet.	Gold Plated Contacts	ACPM-GB-AU
				Bulk Pack	ACPM-GB BULK
	79 [3.115"]———————————————————————————————————	1/4" (6.35mmø) Stereo Phone plug, Diecast Shell,	Standard	ACPS-GN	
		Amphenol	Satin finish, Flexible grommet.	Gold Plated Contacts	ACPS-GN-AU
				Bulk Pack	ACPS-GN BULK
	79 [3.115"]———————————————————————————————————	8:8	1/4" (6.35mmø) Stereo Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPS-GB
		Amphenol		Gold Plated Contacts	ACPS-GB-AU
			Bulk Pack	ACPS-GB BULK	



Amphenol

M SERIES (MUSICIAN RANGE)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	ТҮРЕ	PART NUMBER
	61 [2.402	[194]	1/4" (6.35mmø) Mono Phone plug, Right angle, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPM-RN
	30.6 [1.206] MAX.	.49.3		Gold contacts	ACPM-RN-AU
		, 5, 0		Bulk Pack	ACPM-RN BULK
	61 [2.402*] Aurophanol (YV) (YV)		1/4" (6.35mmø) Mono Phone plug, Right angle, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPM-RB
				Gold contacts	ACPM-RB-AU
		ů O		Bulk Pack	ACPM-RB BULK
	61 [2.402*] Ampheool Office (197) Office		1/4" (6.35mmø) Stereo Phone plug, Right angle, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPS-RN
		- 1		Gold contacts	ACPS-RN-AU
		<u> </u>		Bulk Pack	ACPS-RN BULK
	61 [2.402"] Araphanou 1,50 X, Y,	146.	1/4" (6.35mmø) Stereo Phone plug, Right angle, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPS-RB
		5.0 [.197"]		Gold contacts	ACPS-RB-AU
				Bulk Pack	ACPS-RB BULK





M SERIES / M SERIES II (MUSICIAN RANGE)

PART NUMBER BREAKDOWN

M / M SERIES II (MUSICIAN RANGE)

CONTACT PLATING SHELLFINSH SHELLTYPE **ACP** В ΑU **BULK** E. G. ACPM-GB-AU BULK ACP (Series Prefix), Male, G(Shell Type), Black,
- AU (Gold Plated Contacts), Bulk Packaged. **SERIES PREFIX ACP** Series Prefix **CONTACT TYPE** M 2 pole (Mono) S 3 pole Tip/Ring/Sleeve (Stereo) **SHELL TYPE** G = M Series Straight K M Series II Straight R M Series Right Angle M Series II Right Angle Τ SHELL FINISH N Satin Nickel В Matt Black **CONTACT PLATING** Blank **Nickel Plating** ΑU **Gold Plated PACKAGING** Blank Individual Bags BULK **Bulk Packed**





Amphenol

PLUG AND JACKS TECHNICAL DATA

		VALUE		
GENERAL	Nunber of Contacts	2 Pole (Mono)		
CHARACTERISTICS		3 Pole Tip Ring Sleeve (Stereo)		
	Termination	Solder, PCB or Combo		
	Max. Wire Gauge - Stranded Wire	2 Pole (Mono): AWG 16~1.5mm ²		
		3 Pole (Stereo): AWG 18~1mm ²		
	Flammability rating of insulating plastics	UL94V-0		
	Solderability, complies with	IEC 68-2-20		
	Environmental	Complies with RoHS Directive 2002/95/EC		
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	10A (Depends on Mating Connector and Cable)		
	Typical Contact Resistance	Depends on Mating Connector		
	Insulation resistance (initial)	>2GΩ		
	After Damp Heat Test	≥1GΩ		
	Dielectric Withstand Voltage	2 Pole : 1.5 kV dc		
		3 Pole : 1 kV dc		
CLIMATIC CHARACTERISTICS	Protection Class	IP40		
	Operating Temperature	-25°C to +75°C (-13°F to + 167°F)		
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal Force	≥10N - ≤30N		
	Cable O.D. (Plugs)	6mm (0.236")		
MATERIALS	Connector Shell Material (Plugs)	Diecast Zinc Alloy EZDA No.3		
	Connector Shell Material (Jacks)	UL94 V-0 PBT Modified PPO Resin - Black		
	Connector Shell Finish	Satin Nickel, Nickel or Black Polyester		
	Insulators	UL94 V-0 PBT Resin or Modified PPE Resin and fibreglass laminate		
	Cable Bushing	Santoprene		
	Contacts / Plating (Plugs)	Brass / Ni over Cu (Copper)		
	Contacts / Plating (Jacks)	Brass / Sn (Tin) over Cu (Copper)		

¹⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.