# Storage At Your Fingertips



### **More Power** With USB 3.2 Gen 1

The Marvel M02 Type-A USB flash drive is equipped with a USB 3.2 Gen 1 interface for speedy data transfers. On top of that, with up to 256GB of storage capacity, you'll have more than enough space to take what you need with you.



### Ready, **Inside And Out**

52

On the inside, the Marvel M02 is always ready with True Plug & Play technology, which eliminates the need for external power. On the outside, its aluminum casing is lightweight and durable, while a detachable cap protects the USB connector when not in use.

57 128GF

## USB Flash Drive Marvel M02

### Features

- Super-speed data transfer with USB 3.2 Gen 1 interface
  Instant storage expansion up to 256GB capacity
  Detachable cap protects the USB connector when not in use
  Built-in straphole design for easy attachment to keychains or bags
  True Plug & Play Technology eliminates the need for external power
- Recuva File Recovery allows for recovery of erased files, such as
- Free SP Widget software available for download for backup &

### 16GB | 32GB | 64GB | 128GB | 256GB

### Specifications

- Dimensions: 60.6mm x 19.3mm x 9.9mm
  Weight: 9.5g
  Color: Silver, Blue
  Material: Aluminum + Plastic

- Interface: Type-A USB 3.2 Gen 1 (USB 3.1, USB 3.0, USB 2.0 compatible)
- Capacity: 16GB, 32GB, 64GB, 128GB
- OS Compatibility: Windows 11/10/8.1/8/7/XP, Mac OS 10.3.X and above,

X

- Operating Temperature: 0°C 70°C
  Certification: BSMI, CE, FCC, KC, UKCA, EAC
  Warranty: 5 year limited warranty

C E FC 🗟 💩 [A[ 🛯 🖓 🗛