




18091-810 T-shirt, long-sleeved

Premium - Ladies fit - moisture wicking COOLMAX® PRO - V-neck
MASCOT® ACCELERATE



XS ONE	S ONE	M ONE	L ONE	XL ONE	2XLONE	3XLONE
4XLONE	5XLONE					

55% polyester (COOLMAX® PRO)/45% polyester
230 g/m²




- COOLMAX® ensures efficient moisture wicking, keeps the body dry and prevents chilling.
- Specially designed and fitted for women.
- Perfect as a base layer.

Technical info

Premium. Ladies fit. V-neck. Moisture wicking and insulating.
Print on part of the garment.

User



Logo

You should choose a transfer that can be heated at a maximum of 145 degrees with consideration to print on the product. Remember to check the washing instructions for the chosen transfer before washing the product.

Logo placement:

- T-shirt logo stretch. Left breast. Max 12x12 cm/4.7x4.7 inches
- T-shirt logo stretch. Right breast. Max 12x12 cm/4.7x4.7 inches
- T-shirt logo stretch. On the back. Max 28x28 cm/11x11 inches
- T-shirt logo stretch. On the nape. Max 12x5 cm/4.7x1.9 inches
- Workwear logo. Special placement. Contact to discuss further