

Connector ProTOP

Part no. 15A




- screw terminals

- cable gland and sealing strain relief and protection against kinking enclosure with thread lock and safety slide

Technical specifications

Ampere	16 A
Poles	5 p
Voltage	400 V
Clock position	6 h
Hertz	50-60 Hz
Connection technology	Screw terminals
Contact	standard
Protection type	IP 44
Weight	236 g
Declaration of Conformity	VDE, EAC, Kema

Drawing



Drawing	Amp.		16			32	
3 MB 60	Poles	3	4	5	3	4	5
Dim. in mm	а	160	174	172	214	214	210
	b	57	61	69	75	75	80
	h	83	92	98	100	100	108
	у	16	16	16	22	22	22
Terminal for cond. cross		1	1	1	2.5	2.5	2.5
section (mm²) minmax.		—2.5	—2.5	—2.5	6	—6	-6