



Mobile C30 Swivel, Save, Store.

TYPE-C STORAGE FOR NEXT-GEN DEVICES

With up to 128GB of storage capacity at the ease of a swivel, the Mobile C30 is the perfect solution to gain additional storage space on next-gen devices with limited expansion ports. This is especially relevant for smartphones and tablets. The USB 3.2 Gen 1 interface grants speedy data transfers. Plus, the reversible Type-C connector has a symmetric design that is always right-side-up and the swivel cap has a built-in 4-way positioning system, making it both easy and foolproof to plug in.



DO MORE WITH INSTANT STORAGE EXPANSION

The Mobile C30 USB flash drive makes it easy to move data between USB Type-C devices, including next-gen smartphones, tablets, and notebooks. It's also a cinch to free up space on these devices and quickly make room for new photos, videos, songs, and apps. With USB OTG support, you can directly connect these devices to the Mobile C30 for quick back-ups or to easily access the additional storage space. It's a super efficient way to share data between multiple devices.



USB Flash Drive Mobile C30



Features

- Super-speed data transfer with Type-C USB 3.2 Gen 1 interface
- Up to 128GB of storage capacity for instant storage expansion
- Supports OTG devices for direct access without needing to connect to a computer
- True Plug & Play Technology eliminates the need for external power
- Protected against splashing water, vibration, and dust via COB technology
- Simpler and quicker alternative to cloud storage as the bridge between phones and computers
- 360° swivel cap design makes it easy to access data without ever losing the cap
- Anti-slip treatment on the sides provides a more secure grip and facilitates easier removal from connected devices
- Recuva File Recovery allows for recovery of erased files, such as digital photos, documents, songs, and videos
- Free SP Widget software available for download for backup & restore, AES 256-bit encryption, and cloud storage

Specifications

- Capacity: 16GB, 32GB, 64GB, 128GB
- Dimensions: 54.2mm x 20.0mm x 12.1mm
- Weight: 6.3g
- Color: Black
- Interface: Type-C USB 3.2 Gen 1 (USB 3.1, USB 3.0, USB 2.0 compatible)
- OS Compatibility:
 - Desktop: Windows 11/10/8.1/8/7, Mac OS 10.3.X or later, Linux 2.6.X or later
 - Mobile: Android 4.1.X* or later (*For USB Type-C ready mobile devices)
- Material: Plastic
- Operating Temperature: 0°C - 70°C
- Certification: BSMI, CE, FCC, EAC
- Warranty: 5 year limited warranty