

The dual flash drive for Type-C ready mobile devices



Featuring dual interfaces of USB Type-C and standard Type-A, Mobile C80 can be applied for new-generation devices with USB Type-C ports. USB Type-C, the universal interface of the future, enables easy usage with reversible connector design that allows users to plug the drive into ports no matter which way up it is.



360° swivel cap design

The sturdy 360° swivel cap is designed to protect the connector from outer harm when it is not in use. Moreover, the zinc alloy casing features a sandblasting treatment that enables delicate touch and provides superior resistance to scratches and fingerprints.

Specifications



16GB, 32GB, 64GB

49 4 v 18 0 v 6 6 mm

Dimensions	49.4 X 18.0 X 6.6 mm
Weight	8 g
Material	Zinc alloy
Color	Titanium
Interface	USB-C / USB 3.1 Gen1 / USB 3.0, USB 2.0 compatible
Supported OS	PC- Windows 10/8.1/8/7/Vista/XP, Mac OS 10.3.x or later, Linux 2.6.x or later Mobile device- Android 4.1.X* or later / Windows phone 8* or later (*For USB Type-C ready mobile devices)
Operating Temperature	0° C ~ 70° C
Certification	CE/FCC/BSMI/KCC/Green dot/WEEE/RoHS
Patent	TW Patent No.D172226
Warranty	Lifetime warranty

Features

- · Dual interface for USB Type-C and USB Type-A ports
- 360° swivel cap design

Capacity

- · Ergonomic design, easier to use and grasp
- · Exquisite circular shape, perfectly fitted on a keychain
- Sturdy zinc alloy casing
- · COB (Chip-on-board) technology for water, dust and vibration proof
- Exclusive free-download file management App SP File Explorer
- · Recuva File Recovery, allowing recovery of erased files, such as digital photos, documents, music and videos
- Free-download SP Widget software provides powerful functions such as data backup & restore, AES 256-bit encryption, and cloud storage for efficient data management.