

Do More With Type-C

The Mobile C07 is the perfect solution to gain additional storage space on mobile Type-C devices such as smartphones and tablets.

The USB 3.2 Gen 1 interface grants speedy data transfers, while USB OTG support provides quick back-ups or access to the additional space while – you guessed it – on the go without a computer.



Stores Data, Not Germs

Safety and hygiene are a top priority for the Mobile C07. A laboratory-certified antibacterial coating protects the drive and – most importantly – its users from germs. This is especially useful when sharing the drive with friends or with coworkers in an office environment.

USB Flash Drive

Mobile C07

Features **-**

- Super-speed data transfer with USB 3.2 Gen 1 Type-C interface
- Instant storage expansion up to 256GB capacity
- Laboratory-certified antibacterial coating protects the drive and its users from germs
- True Plug & Play Technology eliminates the need for external power
- Supports OTG devices for direct access without needing to connect to a computer
- Simpler and quicker alternative to cloud storage as the bridge between phones and computers
- Detachable cap protects the USB connector when not in use
- Built-in straphole design for easy attachment to keychains or bags
- Recuva File Recovery allows for recovery of erased files, such as digital photos, documents, songs, and videos
- Free SP Widget software available for download for backup & restore, AES 256-bit encryption, and cloud storage

Specifications

- Dimensions: 54.6mm x 18.9mm x 10.4mm
- Weight: 7.9g
- · Color: Deep Blue, Pink
- · Material: Plastic
- Interface: Type-C USB 3.2 Gen 1 (USB 3.1, USB 3.0, USB 2.0 compatible)
- · Capacity: 16GB, 32GB, 64GB, 128GB, 256GB
- OS Compatibility: Windows 11/10/8.1/8/7/XP, Mac OS 10.3.X and above, Linux 2.6.X and above
- Operating Temperature: 0°C 70°C
- Certification: CE, FCC, BSMI, UKCA, KC
- Warranty: 5 years limited warranty



