



Part Number : [1120361010](#)

Product Description : IP20 Unmanaged PoE Ethernet Switch, 4 PoE Ports + 1 Uplink, 10/100/1000Mb Data Speed

Series Number : 112036

Status : Active

Product Category : Industrial Ethernet Switches

Engineering Number : DRL-251MG



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2021)10043-DC (17 Jan 2022)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Industrial Ethernet Switches
Series	112036
Description	IP20 Unmanaged PoE Ethernet Switch, 4 PoE Ports + 1 Uplink, 10/100/1000Mb Data Speed
Approvals	CE, FCC, UL
IP Rating	IP20
Product Name	IP20 Unmanaged PoE Ethernet Switch
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	PoE
UPC	193264171965

Electrical

Data Speed	Gigabit (10/100/1000Mbps)
EMC	CE, EN 610006-2-4, FCC Part 15, ICES-003
Supply Voltage	24V DC

Physical

Ethernet Connector	RJ45
Housing Depth	119.90mm
Housing Length	120.00mm
Housing Width	50.00mm
MAC Address	8192
Mechanical Shock	IEC 60068-2-27
Mounting Style	DIN Rail, Wall
Net Weight	228.156/g
Packaging Type	Carton
Ports	5
Power Input	24V DC
Temperature Range - Operating	-10° to +60°C
Uplink Connection	RJ45
Vibration	IEC 60068-2-6

This document was generated on Jan 17, 2025