



Part Number : 1120361103

Product Description : IP20 Managed Ethernet Switch, 8 Ports, 10/100/1000Mb Data Speed

Series Number : 218144

Status : Active

Product Category : Industrial Ethernet Switches

Engineering Number : DRL-381MG



---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

## General

Status	Active
Category	Industrial Ethernet Switches
Series	218144
Description	IP20 Managed Ethernet Switch, 8 Ports, 10/100/1000Mb Data Speed
Approvals	CE, FCC, UL
IP Rating	IP20
Product Name	IP20 Managed Ethernet Switch
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	Managed
UPC	78172564341

## Electrical

Data Speed	Gigabit (10/100/1000Mbps)
EMC	CE, EN 610006-2-4, FCC Part 15, ICES-003
Supply Voltage	24V DC

## Physical

Ethernet Connector	RJ45
Housing Depth	120.00mm
Housing Length	160.00mm
Housing Width	50.00mm
MAC Address	8192
Mechanical Shock	IEC 60068-2-27
Mounting Style	DIN Rail, Wall
Net Weight	228.156/g
Packaging Type	Carton
Ports	8
Power Input	24V DC
Temperature Range - Operating	-10° to +60°C
Uplink Connection	N/A
Vibration	IEC 60068-2-6

---

---

This document was generated on Jan 17, 2025