



Part Number : 393570005

Series Number : 39357

Product Category : Terminal Blocks and Barrier Strip

Product Description : 3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 5 Circuits

Status : Active

Engineering Number : MX-MTB05008-0N

Documents & Resources

Drawings

Drawing 393570005_sd.pdf

3D Models and Design Files

3D Model 393570005_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39357
Description	3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 5 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Family	Terminal Blocks & Barrier Strips
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	756054634158

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	17.5A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PC Tail Length	3.50mm
PCB Retention	None

PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	No
Shrouded	Fully
Stackable	Yes
Temperature Range - Operating	-30° to +85°C
Wire Size (AWG)	16, 18, 20, 22, 24, 26, 28
Wire Size mm ²	0.08-1.31