



NCX UF0510

E1630318

PRESSVERKTYG RÖRKABELSKOR(KR/KS/KRF/KSF) 0.5-10mm², & OISOLERADE KABELSKOR 0.5-6.0mm².

Product Properties:

Cycle time	2 s
Inserts exchangeable	Yes
Number of included inserts	1 .
Suitable for	Cable lugs and connectors
With automatic return	Yes
With locking device (for mechanical tools)	Yes
Construction/operation	Mechanical
For component	Non-insulated Cu tube and sheet terminals
Compression shape	Arbour clamping

Dimensions:

Cross section	0.5-10 mm ²
MOQ	1 .
Unit	pcs
Length	235 mm

Approvals:

Compliance:

Conflict minerals	N/A, Contains no conflict minerals
Extended minerals	N/A, contains no extended minerals
Reach	No SVHC (Latest. 14 June 2023)

RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC000168 - Crimp tool cable lugs, cable end sleeves, screen connection
ETIM-Release	7.0
Trademark	NEMIQ
Product Group	One Hand (ratchet)
Search Description	KWB 4099
Alternative SKU	NCXUF0510

Logistic information:

Barcode	733117630549
Country of origin	TW
E-no	E1630318
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	NCX UF0510
Taric code	82032000
Unit	pcs
Units per parcel	
Qty per box	
Units per pallet	